

In most applications, a signal booster (Model Number: B121-000) should be used with this cable to ensure a signal strong enough for your display.

DisplayPort Cable with Latches (M/M) 50 ft. (15.24 m)

MODEL NUMBER: **P580-050**



Highlights

- Digital Video and Audio in one cable
- Supports 1080p resolution
- Small footprint compared to VGA or DVI
- To achieve maximum performance, a signal booster such as the Tripp Lite B121-000 must be used with this cable

Package Includes

DisplayPort Monitor Cable - 50ft

Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Provides up to 1080p resolution
- Monitor Resolution Support: 2560x1600 @ 60Hz, 1920x1200 @ 120Hz
- Supports High Definition Content Protection (HDCP)
- To achieve maximum performance, a signal booster such as the Tripp Lite B121-000 must be used with this cable

Specifications

OVERVIEW	
UPC Code	037332176578
Product Type	Passive
Technology	DisplayPort
PHYSICAL	
Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.2



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	25.40 x 30.48 x 2.54
Shipping Dimensions (hwd / in.)	10.00 x 12.00 x 1.00
Shipping Weight (kg)	0.91
Shipping Weight (lbs.)	2.00
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
SPECIAL FEATURES	
Latching Connector	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>