



## DisplayPort 1.2 to DVI Active Adapter Cable, DP with Latches to DVI (M/M), 6 ft. (1.83 m)

MODEL NUMBER: **P581-006-V2**

Converts a DisplayPort v1.2 video signal for display on a DVI monitor, projector or television.

### Features

#### Send High-Quality DisplayPort v1.2 Video Signals to a DVI Display

- Connects DisplayPort computer to DVI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- DVI-D and DisplayPort male connectors
- No separate adapter required

#### Vibrant, Superior Video Quality

- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals

#### Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- Gold-plated connectors and contacts for excellent conductivity
- Latching Displayport plug for secure connection
- Integral strain relief for long life

## Specifications

OVERVIEW	
UPC Code	037332191977
Technology	DVI; DisplayPort
VIDEO	
Max Supported Video Resolution	1920 x 1200 @60Hz
Max Supported Color Depth	24-bit True Color
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	

### Highlights

- Active adapter cable for use with any Displayport port
- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- No separate adapter required
- Gold-plated connectors and contacts

### Package Includes

- P581-006-V2 DisplayPort 1.2 to DVI Active Adapter Cable, 6 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32~113°F (0~45°C)
Storage Temperature Range	14~158°F (-10~70°C)
Operating Humidity Range	10%~85% RH, Non-Condensing
Storage Humidity Range	5%~90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Displayport Specification	1.2
<b>SPECIAL FEATURES</b>	
Latching Connector	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>