

DisplayPort 1.2 to HDMI Active Adapter Cable (DP with Latches to HDMI M/M), 4K, 3 ft. (0.9 m)

MODEL NUMBER: P582-003-V2-ACT



Highlights

- Active adapter cable for use with any DisplayPort
- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/25/30Hz
- Supports audio and HDCP
- No separate adapter required
- Gold-plated connectors and contacts

Package Includes

- P582-003-V2-ACT DisplayPort 1.2 to HDMI Active Adapter Cable, 3 ft.

Converts a DisplayPort v1.2 audio/video signal for display on an HDMI monitor, projector or television.

Features

Send High-Quality DisplayPort v1.2 Audio/Video Signals to an HDMI Display

- Connects DisplayPort computer to HDMI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- HDMI and latching DisplayPort male connectors
- No separate adapter required

Vibrant, Superior Video Quality

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/25/30Hz
- Supports audio and HDCP
- Active adapter converts Single-Mode and Dual-Mode (DP++) DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals

Superior Materials for Superior Performance

- Gold-plated connectors and contacts for excellent conductivity
- Latching DisplayPort plug for secure connection
- Integral strain relief for long life

Specifications

| OVERVIEW | |
|--------------|-------------------|
| UPC Code | 037332192059 |
| Product Type | Active Cable |
| Technology | HDMI; DisplayPort |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|-------------------------|
| Cable Type | Active |
| VIDEO | |
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 60Hz |
| CONNECTIONS | |
| Side A - Connector 1 | DISPLAYPORT (MALE) |
| Side B - Connector 1 | HDMI (MALE) |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Length (ft.) | 3 |
| Cable Length (m) | 0.91 |
| Cable Length (in.) | 36 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.19 |
| Shipping Weight (kg) | 0.09 |
| FEATURES & SPECIFICATIONS | |
| Displayport Specification | 1.2 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.