

Mini DisplayPort to DisplayPort Adapter Cable (M/M), 4K 60 Hz, Black, 6 ft. (1.8 m)

MODEL NUMBER: P583-006-BK



Connects the Mini DisplayPort (mDP) or Thunderbolt™ output on your computer or laptop to the DisplayPort™ input on a monitor, television or projector.

Features

Sends Ultra High Definition Mini DisplayPort Audio/Video to DisplayPort Monitor

- Connects mDP or Thunderbolt computer or laptop to DisplayPort monitor, TV or projector
- Recommended for displaying video on large monitor or digital sign
- No separate power adapter required

Vibrant Video Quality

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K) @ 60 Hz
- Meets DisplayPort 1.2 standards
- Supports High Bit Rate 2 (HBR2) bandwidth up to 21.6 Gbps
- Backward compatible with previous DisplayPort versions

Superior Materials for Superior Performance

- Locking DisplayPort connector prevents accidental disconnection
- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Integral strain relief reduces stress and adds flexibility

Specifications

Highlights

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K) @ 60 Hz
- Locking DisplayPort connector prevents accidental disconnection
- Gold-plated connectors and contacts for maximum conductivity
- Meets DisplayPort 1.2 standards
- Supports High Bit Rate 2 (HBR2) bandwidth up to 21.6 Gbps

System Requirements

- Source device with Mini DisplayPort or Thunderbolt output
- Display device with DisplayPort input

Package Includes

- P583-006-BK Mini DisplayPort to DisplayPort 4K @ 60 Hz Adapter Cable (M/M), Black, 6 ft.

OVERVIEW

UPC Code

037332203502



Product Type	Passive
Technology	DisplayPort
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Shipping Dimensions (hwd / cm)	15.24 x 10.16 x 1.27
Shipping Dimensions (hwd / in.)	6.00 x 4.00 x 0.50
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.19
ENVIRONMENTAL	
Operating Temperature Range	32 TO 158 F (0 TO 70 C)
Storage Temperature Range	14 TO 176 F (-10 TO 80 C)
Operating Humidity Range	10% TO 85% RH
Storage Humidity Range	5% TO 90% RH
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	MINI DISPLAYPORT (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>