

## Mini DisplayPort Extension Cable, 4K @ 60 Hz, HDCP 2.2 (M/F), 10 ft.

MODEL NUMBER: **P585-010**



Extends your existing Mini DisplayPort (mDP) connection by 10 ft.

### Description

The P585-010 Mini DisplayPort Extension Cable (M/F) attaches to your current mDP cable to extend it by 10 feet. It supports Ultra High Definition video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, allowing you to stream digital video and audio to an mDP display from an mDP computer, such as a MacBook® or Surface® Book, or tablet, including Microsoft's Surface Pro 4. The P585-010 connects to any computer, laptop, mobile device or display that features an mDP, Thunderbolt or Thunderbolt 2 port.

Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Molded nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. A flexible PVC jacket protects twisted 32 AWG data lines and 32 AWG power lines.

### Features

#### Extends an Existing Mini DisplayPort Cable an Extra 10 Ft.

- Female connector attaches to current mDP cable to add length
- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports DisplayPort v1.2a and HDCP 2.2
- Recommended for devices with mDP, Thunderbolt or Thunderbolt 2 ports

#### First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors and gold-plated contacts for optimal signal quality
- Integral strain relief for long life
- Twisted 32/32 AWG data/power lines

### Highlights

- Supports video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Premium foil and braid shielding
- Molded nickel-plated connectors and gold-plated contacts
- Supports DisplayPort™ v1.2a and HDCP 2.2
- Connects to mDP, Thunderbolt™ or Thunderbolt 2 port

### Package Includes

- P585-010 Mini DisplayPort Extension Cable (M/F), 10 ft.



- Flexible PVC jacket and small footprint for easy installation in tight spaces

## Specifications

OVERVIEW	
UPC Code	037332201652
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Cable Length (cm)	304.80
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	MINI DISPLAYPORT (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	DisplayPort
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>