

Mini DisplayPort to HDMI Active Adapter Cable (M/M), 1080p, 6 ft. (1.8 m)

MODEL NUMBER: P586-006-HDMI



Connect a Computer with Mini Displayport or Thunderbolt to a HDMI enabled TV

Features

- 6ft Mini Displayport / Thunderbolt to HDMI Adapter cable
- Supports 1080P video, as well as audio (if video card enabled)
- HDCP compatible
- In-line Passive adapter
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

Specifications

OVERVIEW	
UPC Code	037332180704
Product Type	Active Cable
Technology	HDMI; DisplayPort
VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p)
Max Supported Color Depth	12-bit True Color
HDR Support	No
Chroma Sub Sampling	4:4:4
PHYSICAL	

Highlights

- Supports 1080P 1920x1080 resolution
- Supports Audio
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

System Requirements

- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P586-006-HD-V2A

Package Includes

- 6-ft. (1.83 m) Mini Displayport / Thunderbolt to HDMI Adapter cable



Material of Construction	ABS, PVC
Color	Black
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.8mm
Wire Gauge (AWG)	32
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / cm)	0.64 x 12.70 x 21.08
Shipping Dimensions (hwd / in.)	0.25 x 5.00 x 8.30
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Operating Humidity Range	10 to 85%, Non-Condensing
Storage Humidity Range	5 to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold; Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Displayport Specification	1.1a
HDCP Specification	1.3
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>