



Powering Business Worldwide

TRIPP LITE  
SERIES

# Mini DisplayPort 1.2 to VGA Active Adapter Cable (M/M), 10 ft. (3.1 m)

MODEL NUMBER: **P586-010-VGA-V2**

Converts a Mini DisplayPort v1.2 video signal for display on a VGA monitor, projector or television.

## Features

### Send High-Quality Mini DisplayPort v1.2 Video Signals to a VGA Display

- Connects Mini DisplayPort (or Thunderbolt) computer to VGA-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Mini DisplayPort and HD15 male connectors
- No separate adapter required

### Vibrant, Superior Video Quality

- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals

### Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- Nickel-plated connectors with gold-plated contacts for excellent conductivity
- Integral strain relief for long life

## Highlights

- Active adapter cable for use with any Mini Displayport (or Thunderbolt) port
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Supports computer video resolution up to 1920 x 1200
- Supports HD video resolution up to 1920 x 1080 (1080p)
- No separate adapter required
- Nickel-plated connectors with gold-plated contacts

## Package Includes

- P586-010-VGA-V2 Mini DisplayPort 1.2 to VGA Active Adapter Cable, 10 ft.

## Specifications

OVERVIEW	
UPC Code	037332191861
Product Type	Active Cable
Technology	VGA/SVGA; DisplayPort
Cable Type	Active
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
HDR Support	No
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (MALE)
Connector Plating	Nickel



Powering Business Worldwide

TRIPP LITE  
SERIES

Contact Plating	Gold
Latching or Gripping Connector	No
<b>PHYSICAL</b>	
Color	Black
Material of Construction	ABS, PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.0 +/- 15mm
Wire Gauge (AWG)	32
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	8.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	20.32 x 25.40 x 1.27
Shipping Weight (lbs.)	0.44
Shipping Weight (kg)	0.20
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Operating Humidity Range	0% to 85%, Non-Condensing
Storage Humidity Range	0% to 85%, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
Displayport Specification	1.2
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	3-year limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.