

## Mini DisplayPort to HDMI Active Adapter Cable (M/M), 1080p, 12 ft. (3.7 m)

MODEL NUMBER: P586-012-HDMI



### Highlights

- Connect a computer with a Mini-Displayport video out port to an HDMI-enabled TV
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

### System Requirements

- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P586-012-HD-V2A

### Package Includes

- P586-021-HDMI Mini-DisplayPort to HDMI Cable Adapter (M/M), 12-ft.

### Features

- Connect a computer with a Mini-Displayport video out port to an HDMI-enabled TV
- Supports video resolutions up to 1920 x 1080 (1080p)
- Supports both digital video and audio
- HDCP compatible
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

## Specifications

OVERVIEW	
UPC Code	037332187574
Product Type	Active Cable
Technology	HDMI; DisplayPort
Cable Type	Active
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
Max Supported Color Depth	12-bit True Color
HDR Support	No
Chroma Sub Sampling	4:4:4
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	HDMI (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>PHYSICAL</b>	
Color	Black
Material of Construction	ABS, PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.8mm
Wire Gauge (AWG)	32
Cable Length (ft.)	12
Cable Length (m)	3.66
Cable Length (in.)	144
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.44
Shipping Weight (kg)	0.20
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
Displayport Specification	1.1a
HDCP Specification	1.3
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Warranty Period (U.S. & Canada)	3-year limited warranty
---	-------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.