

Parallel Printer Cable, Bi-Directional (DB25 to Cen36 M/M), 10-ft.

MODEL NUMBER: P602-010



Description

Tripp Lite's 10-ft. bi-directional parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. The cable has DB25 male/Cent36 male connectors and supports bi-directional communication. It is manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection. Bi-directional communication allows your printer to broadcast printer error messages back to network computers. Use IEEE cable if IEEE specifications are required.

Features

- Supports bi-directional communication
- Length 10-ft. Connectors: DB25 male/Cent36 male
- Superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold
- Use IEEE cable if IEEE specifications are required

Specifications

OVERVIEW UPC Code 037332013446 Technology Parallel CONNECTIONS DB25 (MALE) Side A - Connector 1 DB25 (MALE) Side B - Connector 1 CENTRONICS 36 (MALE)

Highlights

- Superior molded cables with integral strain relief and foilshielding for maximum EMI/RFI protection
- Provides superior conductivity and support for high-speed bidirectional printing

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with Bi-Directional communication (although not essential).

Package Includes

• 10-ft. Bidir Parallel Cable Cen36M to DB25M



PHYSICAL	
Color	Beige
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Weight (lbs.)	0.55
Shipping Weight (kg)	0.25
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard

Cleveland, OH 44122

United States

https://tripplite.eaton.com

© 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.