



Powering Business Worldwide

# 25-ft. Premium Bi-Directional Parallel Cable (DB25M to Cen36M)

MODEL NUMBER: P604-025



### Highlights

- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- Provides superior conductivity and support for high-speed bi-directional printing

### System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with Bi-Directional communication (although not essential)

### Package Includes

- 25-ft. Premium Bidir Parallel Cable Cen36M to DB25M

### Description

Tripp Lite's 25-ft. premium bi-directional parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. The cable has DB25 male/Cent36 male connectors and supports bi-directional communication. It is manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection. Bi-directional communication allows your printer to broadcast printer error messages back to network computers. Use IEEE cable if IEEE specifications are required. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- Supports bi-directional communication
- Length: 25-ft. Connectors: DB25 male/Cent36 male
- Premium molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold
- Use IEEE cable if IEEE specifications are required

## Specifications

OVERVIEW	
UPC Code	037332013507
CONNECTIONS	
Side A - Connector 1	DB25 (MALE)
Side B - Connector 1	CENTRONICS 36 (MALE)
PHYSICAL	



Powering Business Worldwide

Color	Beige
Cable Length (ft.)	25
Cable Length (m)	7.62
Shipping Dimensions (hwd / in.)	12.50 x 10.00 x 1.25
Shipping Dimensions (hwd / cm)	31.75 x 25.40 x 3.18
Shipping Weight (lbs.)	1.40
Shipping Weight (kg)	0.64
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.