



Powering Business Worldwide

## Computer Cable, 20-ft. AB Parallel Gold Cable, Cen36M to DB25M

MODEL NUMBER: P606-020



### Description

Tripp Lite's 20-ft. A-B gold parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing. The cable features gold plated DB25 male/Cen36 male connectors and gold plated copper contacts for superior conductivity. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing
- Length: 20-ft. Connectors: DB25 male/Cen36 male
- Gold plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Specifications

OVERVIEW	
UPC Code	037332013583
Technology	Parallel

### Highlights

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing.
- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- Gold-plated connectors provide superior conductivity and support high-speed bi-directional printing

### System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with high-speed Bi-Directional communication (although not essential).

### Package Includes

- 20-ft. AB Parallel Gold Cable Cen36M to DB25M

CONNECTIONS	
Side A - Connector 1	DB25 (MALE)
Side B - Connector 1	CENTRONICS 36 (MALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	20
Cable Length (m)	6.10
Shipping Dimensions (hwd / in.)	12.75 x 10.00 x 1.25
Shipping Dimensions (hwd / cm)	32.38 x 25.40 x 3.18
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.