

6-ft. IEEE 1284 AC Parallel Cable (DB25M to MicroCen36M)

MODEL NUMBER: P608-006



Description

Tripp Lite's 6-ft. IEEE 1284 A-C parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Micro Centronics 36 female parallel port. The cable has DB25 male/MicroCent36 male connectors and supports high-speed IEEE 1284 bi-directional communication. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems.

Features

- Supports high-speed IEEE 1284 bi-directional communication (modes: standard compatible nibble byte ECP and EPP)
- Length: 6-ft. Connectors: DB25 male/MicroCent36 male
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold

Specifications

OVERVIEW		
UPC Code	037332013613	
CONNECTIONS		
Side A - Connector 1	DB25 (MALE)	
Side B - Connector 1	MINI CENTRONICS 36 (MALE)	

Highlights

- Superior molded cables with integral strain relief and foilshielding for maximum EMI/RFI protection
- IEEE 1284 cables' gold-plated connectors provide superior conductivity and support highspeed bi-directional printing

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Micro Centronics 36 Female parallel port with high-speed IEEE 1284 Bi-Directional communication.

Package Includes

 6-ft. IEEE 1284 AC Parallel Cable DB25M to MicroCen36M



PHYSICAL		
Color	Beige	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	11.75 x 7.00 x 1.00	
Shipping Dimensions (hwd / cm)	29.84 x 17.78 x 2.54	
Shipping Weight (lbs.)	0.55	
Shipping Weight (kg)	0.25	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard

Cleveland, OH 44122

United States

https://tripplite.eaton.com

© 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.