



Powering Business Worldwide

Computer Cable, 10-ft. IEEE 1284 AC Parallel Cable DB25M to MicroCen36M

MODEL NUMBER: P608-010



Highlights

- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- IEEE 1284 cables' gold-plated connectors provide superior conductivity and support high-speed bi-directional printing

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Micro Centronics 36 Female parallel port with high-speed IEEE 1284 Bi-Directional communication

Package Includes

- 10-ft. IEEE 1284 AC Parallel Cable DB25M to MicroCen36M

Description

Tripp Lite's 10-ft. IEEE 1284 A-C parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Micro Centronics 36 female parallel port. The cable has DB25 male/MicroCent36 male connectors and supports high-speed IEEE 1284 bi-directional communication. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Supports high-speed IEEE 1284 bi-directional communication (modes: standard compatible nibble byte ECP and EPP)
- Length: 10-ft. Connectors: DB25 male/MicroCent36 male
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
UPC Code	037332013620
CONNECTIONS	
Side A - Connector 1	DB25 (MALE)

Side B - Connector 1	MINI CENTRONICS 36 (MALE)
PHYSICAL	
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	11.75 x 7.00 x 1.00
Shipping Dimensions (hwd / cm)	29.84 x 17.78 x 2.54
Shipping Weight (lbs.)	0.81
Shipping Weight (kg)	0.37
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.