

USB Cable Kit for KVM Switch B006-VU4-R, 6-ft.

MODEL NUMBER: P758-006



Description

Tripp Lite's 6-ft. USB KVM cable kit connects a USB computer to a B006-VU4-R KVM switch. The KVM switch side of the cable kit consists of a USB Type B Male cable and a SVGA (HD15) Female monitor cable. The computer side of the cable kit consists of a USB Type A Male cable and a SVGA (HD15) Male monitor cable. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

Features

- Required to connect a USB computer to a B006-VU4-R KVM switch
- KVM switch side of the cable kit consists of a USB Type B Male cable and a SVGA (HD15) Female monitor cable
- Computer side of the cable kit consists of a USB Type A Male cable and a SVGA (HD15) Male monitor cable
- Molded ends with easy-grip textured overmold
- Supports any VGA/SVGA monitor
- Constructed of mini-coax (RGB) and paired video wire
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Hi-Resolution cable

Specifications

OVERVIEW	
UPC Code	037332014986
INPUT	

Highlights

- Required to connect a USB computer to the B006-VU4-R KVM switch
- KVM switch side of the cable kit consists of a USB Type B Male cable and a SVGA (HD15) Female monitor cable
- Computer side of the cable kit consists of a USB Type A Male cable and a SVGA (HD15) Male monitor cable

System Requirements

- A USB computer
- A USB KVM switch (model # B006-VU4-R).

Package Includes

- 6-ft. USB Cable Kit for the B006-VU4-R KVM Switch



Cable Length (ft.)	6
Cable Length (m)	1.83
PHYSICAL	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
CONNECTIONS	
KVM Switch Side 1	HD15 (Female)
KVM Switch Side 2	USB B (Male)
Computer Side 1	HD15 (Male)
Computer Side 2	USB A (Male)
FEATURES & SPECIFICATIONS	
Technology	USB; VGA/SVGA
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>