

DVI to USB-A Dual KVM Cable Kit - (2x Male/2x Male), 1920 x 1200 (1080p) @ 60 Hz, 10 ft. (3.05 m)

MODEL NUMBER: P760-010-DVI



Connects a DVI monitor and USB-enabled keyboard and mouse to the DVI port on a KVM switch located up to 10 ft. away.

Features

10 ft. Cable Kit with Dual DVI and USB Ports Connect Monitor/Keyboard/Mouse to Your KVM This KVM cable Kit allows you to connect a DVI monitor and USB keyboard/mouse to your switch's DVI port. Designed as a replacement for the 6-ft. (1.83 m) accessory cable included with Tripp Lite's B021-000-19-HD or B021-000-19-HD2 1U rack-mount consoles, the 10-ft. (3.05 m) P760-010-DVI is ideal for scenarios in which a longer cable is needed. It features two male DVI connectors and two male USB-A connectors, and supports DVI video resolutions up to 1920 x 1200, including 1080p, at 60 Hz. Its slim diameter cuts down on cable clutter around your rack.

Specifications

OVERVIEW	
UPC Code	037332239488
Product Type	Cable Kit
Accessories Type	Cable Kit
Technology	DVI; USB 2.0 (High Speed)
VIDEO	
Max Supported Video Resolution	1920 x 1200 @ 60 Hz
PHYSICAL	
Color	Black

Highlights

- Ideal replacement cable in applications where a longer KVM cord is needed
- Connects USB keyboard/mouse to your KVM switch's DVI port
- DVI monitor connection supports HD resolutions up to 1920 x 1200 @ 60 Hz
- Slim diameter cuts down on clutter and makes cable easier to route and connect

Applications

- Connect a keyboard, mouse and DVI-enabled monitor to a KVM switch
- Upgrade or replace a worn or lost KVM cable
- Extend the distance between the switch and monitor/keyboard/mouse to 10 ft.

Package Includes

- P760-010-DVI DVI to USB-A Dual KVM Cable Kit (2xM/2xM), 10 ft.



Cable Length (ft.)	10
Cable Length (in.)	120
ENVIRONMENTAL	
Operating Temperature Range	14 ~ 122F (-10 ~ 50C)
Storage Temperature Range	5 ~ 140F (-15 ~ 60C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	DVI-I DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 1	DVI-I DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	USB A (MALE)
Side B - Connector 3	USB A (MALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>