

Daisy Chain Cable for NetDirector KVM Switch B020-Series and KVM B022-Series, 15 ft. (4.57 m)

MODEL NUMBER: P772-015



Description

Tripp Lite's 15-ft. (4.57 m) daisy chain cable is designed to connect a B020 / B022 NetDirector KVM switch to another NetDirector KVM switch, allowing for the expansion of the number of computers/servers that can be controlled from a single keyboard, mouse and monitor. This premium cable features a PVC jacket and double shielding (foil and braid) for maximum EMI/RFI protection. The cable's DB25 connectors are molded with integral strain relief and easy-grip textured overmold.

Features

- Links a B020 / B022 NetDirector KVM switch to another NetDirector KVM switch, allowing for the expansion of the number of computers/servers that can be controlled from a single keyboard, mouse and monitor
- Length: 15-ft. (4.57 m)
- Connectors: DB25 Male to DB25 Female
- Features a PVC jacket and double shielding (foil and braid) for maximum EMI/RFI protection
- Molded connectors with integral strain relief and easy-grip textured overmold

Specifications

| OVERVIEW | |
|--------------------|--------------|
| UPC Code | 037332122841 |
| INPUT | |
| Cable Length (ft.) | 15 |

Highlights

- Required to daisy-chain multiple B020 / B022 NetDirector KVM switches
- Allows for expanding the number of computers/servers that can be controlled by a single keyboard, mouse and monitor
- This premium cable features a PVC jacket and double shielding (foil and braid) for maximum EMI/RFI protection
- DB25 connectors are molded with integral strain relief and easy-grip textured overmold

System Requirements

- A Tripp Lite B020 / B022 NetDirector KVM switch connecting to another NetDirector KVM Switch

Package Includes

- 15-ft. (4.57 m) Daisychain Cable for Tripp Lite's B020 / B022 NetDirector KVM Switch



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---------------------------|
| Cable Length (m) | 4.57 |
| PHYSICAL | |
| Shipping Dimensions (hwd / cm) | 30.48 x 35.56 x 1.27 |
| Shipping Dimensions (hwd / in.) | 12.00 x 14.00 x 0.50 |
| Shipping Weight (kg) | 0.50 |
| Shipping Weight (lbs.) | 1.10 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>