

Daisy Chain Cable for NetController KVM Switches B040-Series and B042-Series, 10 ft. (3.05 m)

MODEL NUMBER: P781-010



Highlights

- Molded HD15 Male/Female, 10-ft. (3.05 m)
- Double Shielded
- For Daisy Chaining B040 and B042 KVM switches

System Requirements

Use only with Tripp Lite B040 and B042 series KVM switches, to daisy chain additional KVM switches.

Package Includes

10-ft. (3.05 m) HD15 Male/Female B040 / B042 KVM Daisy Chain Cable

Description

Molded, 10-ft. (3.05 m), HD15 Male/Female Daisy-Chain cable, specifically wired for Tripp Lite B040 and B042 series KVM switches. Double shielded and fully molded construction for optimum video transfer and long life.

Features

- Daisy Chain cable for Tripp Lite B040 and B042 series KVM switches
- Fully molded construction, with double shielding
- HD15 Male/Female 10-ft. (3.05 m)

Specifications

OVERVIEW	
UPC Code	037332146502
PHYSICAL	
Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 17.78
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 7.00
Shipping Weight (kg)	0.23



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	0.50
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>