

HDMI KVM Cable Kit - 4K HDMI, USB 2.0, 3.5 mm Audio (M/M), Black, 6 ft. (1.83 m)

MODEL NUMBER: P782-006-HA



Convenient 3-in-1 cable kit connects a computer or server with HDMI, USB and/or 3.5 mm ports to a compatible Tripp Lite KVM switch.

Features

6-ft. (1.83 m) Cables Connect Your Computer's HDMI, USB and Audio Ports to a Tripp Lite KVM Switch This HDMI cable kit includes three cables for connecting your computer to a KVM switch. Recommended for the Tripp Lite B024-HU08 and B024-HU16 KVM switches, the kit saves you money and cuts down on unnecessary clutter by combining necessary cables into one convenient bunch.

HDMI The HDMI cable lets you view the video content of your computer via the console's connected monitor. It supports Ultra HD resolutions up to 3840 x 2160 (@ 30 Hz) for crystal-clear 4K x 2K video.

USB The USB cable connects the KVM switch's USB-B port to your computer's USB-A port. It enables you to control all connected computers from one centralized keyboard/mouse, while also accessing external flash drives, printers, scanners or other devices connected to the switch's USB peripheral ports. The cable supports USB 2.0 data transfer speeds up to 480 Mbps.

3.5 mm Audio The 3.5 mm stereo cable connects external multimedia speakers, a microphone or headphones and share them between computers.

Quality Construction Provides Superior Signal Transfer Integral strain relief gives the cables extra flexibility, reduces stress, and helps the cables move freely without cracking or breaking loose from the connectors. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated connectors with gold-plated contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference.

Specifications

OVERVIEW	
UPC Code	037332252647

Highlights

- Includes 6-ft. (1.83 m) HDMI, USB 2.0 A/B and 3.5 mm stereo audio cables in one kit
- Integral strain relief helps cables move freely without stress or cracking
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Supports UHD resolutions up to 3840 x 2160 (@ 30 Hz) for crystal-clear 4K x 2K video

Applications

- Connect an HDMI monitor, keyboard/mouse and audio equipment, such as speakers or a microphone, to your Tripp Lite KVM switch

System Requirements

- Computer with USB, HDMI and/or 3.5 mm ports
- B024-HU08 or B024-HU16 KVM switch

Package Includes

- P569-006 HDMI cable (M/M), 6 ft.
- U022-006 USB-A to USB-B cable (M/M), 6-ft. (1.83 m)
- P312-006 3.5 mm audio cable (M/M), 6-ft. (1.83 m)

Accessory Type	Cable Kit
Technology	HDMI; Stereo Audio
Accessory Class	KVM Switch Accessories
VIDEO	
Max Supported Video Resolution	3840 x 2160 @ 30 Hz
AUDIO	
Audio Specification	Stereo Audio
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 1.00
Shipping Weight (kg)	0.20
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	0 TO 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side A - Connector 2	USB A (MALE)
Side A - Connector 3	3.5MM (MALE)
Side B - Connector 1	HDMI (MALE)
Side B - Connector 2	USB B (MALE)
Side B - Connector 3	3.5MM (MALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty