

DisplayPort KVM Cable Kit - DP, USB, 3.5 mm Audio (3xM/3xM) + USB (M/M), 4K, 4:4:4, 6 ft. (1.83 m), Black

MODEL NUMBER: P783-006-U



DisplayPort KVM cable kit with DisplayPort, USB A/B and 3.5 mm plugs connects your computer to a Tripp Lite B002-HD1AC4 NIAP KVM.

Features

6 ft. Cables Connect Your DisplayPort Computer to a Tripp Lite NIAP KVM Switch with CAC This DisplayPort cable kit includes two 6-ft. (1.83 m) cables for connecting a computer to a KVM switch with a Common Access Card (CAC) port. The P783-006 features DisplayPort, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The U022-006 is a USB cable that connects to the KVM's CAC port for accessing smart cards, scanners and biometric readers, including fingerprint readers, to bolster security.

Specifically Designed for Select Tripp Lite KVMs to Save You Time and Money Recommended for the Tripp Lite B002-HD1AC4 NIAP KVM, the DisplayPort cable supports video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz with true 4:4:4 chroma subsampling. The USB cables also support USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and costs.

Highlights

- Cuts cable clutter and saves money by combining essential KVM cables into just 2
- 6-ft. (1.83 m) 3-in-1 DP, USB A/B and 3.5 mm audio cable connects KVM to your computer
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports true 4:4:4 chroma subsampling to meet latest color standards
- 6-ft. (1.83 m) USB A/B cable included for KVM's CAC port (smart cards, scanners, etc.)

Applications

- Connect a headless computer to a Tripp Lite KVM switch with CAC support
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter and save money by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 6-ft. (1.83 m)

System Requirements

- Tripp Lite B002-HD1AC4 NIAP KVM or other compatible KVM switch

Package Includes

- P783-006 DisplayPort KVM cable kit, 3 in 1 (M/M), 6-ft. (1.83 m)
- U022-006 USB A/B cable (M/M),



6-ft. (1.83 m)

Specifications

OVERVIEW	
UPC Code	037332241658
Technology	DisplayPort; USB
VIDEO	
Max Supported Video Resolution	3840 x 2160 @ 60Hz
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Shipping Dimensions (hwd / cm)	2.54 x 20.32 x 27.30
Shipping Dimensions (hwd / in.)	1.00 x 8.00 x 10.75
Shipping Weight (kg)	0.30
Shipping Weight (lbs.)	0.66
ENVIRONMENTAL	
Operating Temperature Range	14 ~ 122F (-10 ~ 50C)
Storage Temperature Range	5 ~ 140F (-15 ~ 60C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	3.5MM (MALE); DISPLAYPORT (MALE); USB A (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	3.5MM (MALE); DISPLAYPORT (MALE); USB B (MALE)
Side B - Connector 2	USB B (MALE)
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
HDCP Specification	2.2



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Specification	USB 2.0 (up to 480 Mbps)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>