

Dual DisplayPort KVM Cable Kit - DP, USB, 3.5 mm Audio (3xM/3xM) + DP (M/M), 4K, 4:4:4, 10 ft., Black

MODEL NUMBER: P783-010-DP



Dual DisplayPort KVM cable kit with DP, USB A/B and 3.5 mm plugs connects your computer to a Tripp Lite B002-DP2A4 NIAP KVM.

Features

10 ft. Cables Connect Your Computer and 2 DisplayPort Monitors to a Tripp Lite NIAP KVM

This DisplayPort cable kit includes two 10-foot cables for connecting a computer with two monitors to a KVM switch. The P783-010 features DisplayPort, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The P580-010 is a DisplayPort cable with male connectors on each end.

Specifically Designed for Select Tripp Lite KVMs to Save You Time and Money

Recommended for the Tripp Lite B002-DP2A4 NIAP KVM, the cables support DisplayPort video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz with true 4:4:4 chroma subsampling. They are compatible with HDCP 2.2 and DisplayPort 1.2 standards. The P783-010 also supports USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and save money.

Highlights

- Cuts cable clutter and saves money by combining essential KVM cables into just 2
- Includes 10 ft. DisplayPort cable and 10 ft. 3-in-1 DP, USB and 3.5 mm audio cable
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports true 4:4:4 chroma subsampling to meet latest color standards
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a headless computer with dual displays to a Tripp Lite KVM switch
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter and save money by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 10 ft.

System Requirements

- Tripp Lite B002-DP2A4 NIAP KVM or other compatible KVM switch

Package Includes

- P783-010 DisplayPort KVM cable kit, 3 in 1 (M/M), 10 ft.
- P580-010 DisplayPort monitor



cable (M/M), 10 ft.

Specifications

OVERVIEW	
UPC Code	037332241641
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Weight (kg)	0.55
Shipping Weight (lbs.)	1.22
ENVIRONMENTAL	
Operating Temperature Range	14 ~ 122F (-10 ~ 50C)
Storage Temperature Range	5 ~ 140F (-15 ~ 60C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	3.5MM (MALE); DISPLAYPORT (MALE); USB A (MALE)
Side A - Connector 2	DISPLAYPORT (MALE)
Side B - Connector 1	3.5MM (MALE); DISPLAYPORT (MALE); USB B (FEMALE)
Side B - Connector 2	DISPLAYPORT (MALE)
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	3840 x 2160 @ 60Hz
Displayport Specification	1.2
HDCP Specification	2.2
USB Specification	USB 2.0 (up to 480 Mbps)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Technology	DisplayPort; USB
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>