

DVI KVM Cable Kit, 3 in 1 - DVI, USB, 3.5 mm Audio (3xM/3xM), 6 ft. (1.83 m)

MODEL NUMBER: P784-006



3-in-1 KVM cable kit with DVI, USB A/B and 3.5 mm plugs connects your computer to a Tripp Lite B002-DV1A2 or B002-DV1A4 NIAP KVM.

Features

6 ft. 3-in-1 Cable Connects Your DVI Computer to a Tripp Lite NIAP KVM Switch This cable features 24-pin dual-link DVI-I, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. Designed specifically for the Tripp Lite B002-DV1A2 and B002-DV1A4 NIAP KVMs, the six-foot cable supports DVI video resolutions up to 2560 x 1600 (including 1080p) at 60 Hz, as well as USB 2.0 data transfer speeds up to 480 Mbps. By combining three different cables into one convenient cord, you cut down on unnecessary clutter and save money.

Highlights

- Cuts cable clutter and saves money by combining 3 essential KVM cables into one
- Delivers HD picture quality at resolutions up to 2560 x 1600 (1080p) @ 60 Hz
- Transfers data at reliable USB 2.0 speeds up to 480 Mbps
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a headless computer to a Tripp Lite KVM switch
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter by replacing multiple cables with one new one
- Extend the distance between the KVM switch and computer to 6 ft.

System Requirements

- Tripp Lite B002-DV1A2 or B002-DV1A4 NIAP KVM or other compatible KVM switch

Package Includes

- P784-006 DVI KVM cable kit, 3 in 1 (M/M), 6 ft.

Specifications

OVERVIEW	
UPC Code	037332242303
Technology	DVI; USB



VIDEO	
Max Supported Video Resolution	2560 x 1600P @ 60 Hz
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50
Shipping Weight (kg)	0.32
ENVIRONMENTAL	
Operating Temperature Range	14 ~ 122F (-10 ~ 50C)
Storage Temperature Range	5 ~ 140F (-15 ~ 60C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB A (MALE)
Side B - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB B (MALE)
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>