

## Dual DVI KVM Cable Kit - DVI, USB, 3.5 mm Audio (3xM/3xM) + DVI (M/M), 1080p, 6 ft., Black

MODEL NUMBER: P784-006-DV



Dual DVI KVM cable kit with DVI, USB A/B and 3.5 mm plugs connects your computer to a Tripp Lite B002-DV2A4 NIAP KVM.

### Features

#### 6 ft. Cables Connect Your Computer and 2 DVI Monitors to a Tripp Lite NIAP KVM Switch

This DVI cable kit includes two 6-foot cables for connecting a computer with two monitors to a KVM switch. The P784-006 features 24-pin dual-link DVI-I, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The P560-006-DLI is a dual-link DVI-I cable with male connectors on each end. Designed specifically for the Tripp Lite B002-DV2A4 NIAP KVM, the cables supports DVI video resolutions up to 2560 x 1600 (including 1080p) at 60 Hz. The P784-006 also supports USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and save money.

### Highlights

- Cuts cable clutter and saves money by combining essential KVM cables into just 2
- Includes 6 ft. DVI cable and 6 ft. 3-in-1 DVI, USB and 3.5 mm audio cable
- Delivers HD picture quality at resolutions up to 2560 x 1600 (1080p) @ 60 Hz
- Transfers data at reliable USB 2.0 speeds up to 480 Mbps
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Connect a headless computer with dual displays to a Tripp Lite KVM switch
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 6 ft.

### System Requirements

- Tripp Lite B002-DV2A4 NIAP KVM or other compatible KVM

### Package Includes

- P784-006 DVI KVM cable kit, 3 in 1 (M/M), 6 ft.
- P560-006-DLI DVI monitor cable (M/M), 6 ft.



## Specifications

<b>OVERVIEW</b>	
UPC Code	037332242327
<b>INPUT</b>	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Weight (kg)	0.58
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 ~ 122F (-10 ~ 50C)
Storage Temperature Range	5 ~ 140F (-15 ~ 60C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB A (MALE)
Side A - Connector 2	DVI-I DUAL LINK (MALE)
Side B - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB B (MALE)
Side B - Connector 2	DVI-I DUAL LINK (MALE)
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
Max Supported Video Resolution	2560 x 1600P @ 60 Hz
USB Specification	USB 2.0 (up to 480 Mbps)
Technology	DVI; Stereo Audio; USB
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>