

DVI KVM Cable Kit - DVI, USB, 3.5 mm Audio (3xM/3xM) + USB (M/M) + DVI (M/M), 1080p, 6 ft., Black

MODEL NUMBER: P784-006-DVU



DVI KVM cable kit includes cables with DVI, USB and 3.5 mm plugs for connecting your computer to a Tripp Lite B002-DV2AC4 NIAP KVM.

Features

6 ft. Cables Connect Your DVI Computer to a Tripp Lite NIAP KVM Switch with CAC

This DVI cable kit includes three 6-foot cables for connecting a computer with two monitors to a KVM switch with a Common Access Card (CAC) port. The P784-006 features 24-pin dual-link DVI-I, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The P560-006-DLI is a dual-link DVI-I cable with male connectors on each end. The U022-006 is a USB cable that connects to the KVM's CAC port for accessing smart cards, scanners and biometric readers, including fingerprint readers, to bolster security.

Specifically Designed for Select Tripp Lite KVMs to Save You Time and Money

Recommended for the Tripp Lite B002-DV2AC4 NIAP KVM, the DVI cables support video resolutions up to 2560 x 1600 (including 1080p) at 60 Hz. The USB cables also support USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and costs.

Highlights

- 6 ft. 3-in-1 DVI, USB A/B and 3.5 mm audio cable connects KVM to your computer
- 6 ft. DVI cable included for connecting a second monitor to the KVM switch
- Delivers HD picture quality at resolutions up to 2560 x 1600 (1080p) @ 60 Hz
- 6 ft. USB A/B cable included for KVM's CAC port (smart cards, scanners, etc.)
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a headless computer with dual displays to a Tripp Lite KVM switch with CAC support
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 6 ft.

System Requirements

- Tripp Lite B002-DV2AC4 NIAP KVM or other compatible KVM switch

Package Includes

- P784-006 DVI KVM cable kit, 3 in 1 (M/M), 6 ft.
- P560-006-DLI DVI monitor cable (M/M), 6 ft.



- U022-006 USB A/B cable (M/M),
6 ft.

Specifications

OVERVIEW	
UPC Code	037332242341
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Weight (kg)	0.65
ENVIRONMENTAL	
Operating Temperature Range	14 ~ 122F (-10 ~ 50C)
Storage Temperature Range	5 ~ 140F (-15 ~ 60C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB A (MALE)
Side A - Connector 2	DVI-I DUAL LINK (MALE)
Side A - Connector 3	USB A (MALE)
Side B - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB B (MALE)
Side B - Connector 2	DVI-I DUAL LINK (MALE)
Side B - Connector 3	USB B (MALE)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	2560 x 1600P @ 60 Hz
USB Specification	USB 2.0 (up to 480 Mbps)
Technology	DisplayPort; Stereo Audio; USB



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>