

Dual DVI KVM Cable Kit - DVI, USB, 3.5 mm Audio (3xM/3xM) + DVI (M/M), 10 ft. (3.05 m)

MODEL NUMBER: P784-010-DV



Dual DVI KVM cable kit with DVI, USB A/B and 3.5 mm plugs connects your computer to a Tripp Lite B002-DV2A4 NIAP KVM.

Features

10-ft. (3.05 m) Cables Connect Your Computer and 2 DVI Monitors to a NIAP KVM Switch

This DVI cable kit includes two 10-ft. (3.05 m) cables for connecting a computer with two monitors to a KVM switch. The P784-010 features 24-pin dual-link DVI-I, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The P560-010-DLI is a dual-link DVI-I cable with male connectors on each end. Designed specifically for the B002-DV2A4 NIAP KVM, the cables supports DVI video resolutions up to 2560 x 1600 (including 1080p) at 60 Hz. The P784-010 also supports USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and save money.

Highlights

- Cuts cable clutter and saves money by combining essential KVM cables into just 2
- Includes 10-ft. (3.05 m) DVI cable and 10-ft. (3.05 m) 3-in-1 DVI, USB and 3.5 mm audio cable
- Delivers HD picture quality at resolutions up to 2560 x 1600 (1080p) @ 60 Hz
- Transfers data at reliable USB 2.0 speeds up to 480 Mbps
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a headless computer with dual displays to a Tripp Lite KVM switch
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 10 ft.

System Requirements

- B002-DV2A4 NIAP KVM or other compatible KVM switch

Package Includes

- P784-010 DVI KVM cable kit, 3 in 1 (M/M), 10-ft. (3.05 m)
- P560-010-DLI DVI monitor cable (M/M), 10-ft. (3.05 m)

Specifications

OVERVIEW	
UPC Code	037332242334
Accessory Type	Cable Kit
Technology	DVI; Stereo Audio
Accessory Class	KVM Switch Accessories
VIDEO	

Max Supported Video Resolution	2560 x 1600P @ 60 Hz
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	10.00 x 14.00 x 14.00
Shipping Weight (kg)	0.84
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB A (MALE)
Side A - Connector 2	DVI-I DUAL LINK (MALE)
Side B - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB B (MALE)
Side B - Connector 2	DVI-I DUAL LINK (MALE)
Connector Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty