

Dual DVI KVM Cable Kit - DVI, USB, 3.5 mm Audio (3xM/3xM) + DVI (M/M), 1080p, 10 ft., Black

MODEL NUMBER: **P784-010-DV**



Dual DVI KVM cable kit with DVI, USB A/B and 3.5 mm plugs connects your computer to a Tripp Lite B002-DV2A4 NIAP KVM.

Features

10 ft. Cables Connect Your Computer and 2 DVI Monitors to a Tripp Lite NIAP KVM Switch

This DVI cable kit includes two 10-foot cables for connecting a computer with two monitors to a KVM switch. The P784-010 features 24-pin dual-link DVI-I, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The P560-010-DLI is a dual-link DVI-I cable with male connectors on each end. Designed specifically for the Tripp Lite B002-DV2A4 NIAP KVM, the cables support DVI video resolutions up to 2560 x 1600 (including 1080p) at 60 Hz. The P784-010 also supports USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and save money.

Highlights

- Cuts cable clutter and saves money by combining essential KVM cables into just 2
- Includes 10 ft. DVI cable and 10 ft. 3-in-1 DVI, USB and 3.5 mm audio cable
- Delivers HD picture quality at resolutions up to 2560 x 1600 (1080p) @ 60 Hz
- Transfers data at reliable USB 2.0 speeds up to 480 Mbps
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a headless computer with dual displays to a Tripp Lite KVM switch
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 10 ft.

System Requirements

- Tripp Lite B002-DV2A4 NIAP KVM or other compatible KVM switch

Package Includes

- P784-010 DVI KVM cable kit, 3 in 1 (M/M), 10 ft.
- P560-010-DLI DVI monitor cable (M/M), 10 ft.



Specifications

OVERVIEW	
UPC Code	037332242334
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	10.00 x 14.00 x 14.00
Shipping Weight (kg)	0.84
ENVIRONMENTAL	
Operating Temperature Range	14 ~ 122F (-10 ~ 50C)
Storage Temperature Range	5 ~ 140F (-15 ~ 60C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB A (MALE)
Side A - Connector 2	DVI-I DUAL LINK (MALE)
Side B - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB B (MALE)
Side B - Connector 2	DVI-I DUAL LINK (MALE)
Connector Plating	Gold
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	2560 x 1600P @ 60 Hz
USB Specification	USB 2.0 (up to 480 Mbps)
Technology	DVI; Stereo Audio; USB
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>