

DVI KVM Cable Kit - DVI, USB, 3.5 mm Audio (3xM/3xM) + USB (M/M), 1080p, 10 ft. (3.05 m)

MODEL NUMBER: P784-010-U



Dual DVI KVM cable kit with DVI, USB A/B and 3.5 mm plugs connects your computer to a Tripp Lite B002-DV1AC4 or B002-DV1AC8 NIAP KVM.

Features

10-ft. (3.05 m) Cables Connect Your DVI Computer to a NIAP KVM Switch with CAC This DVI cable kit includes two 10-ft. (3.05 m) cables for connecting a computer to a KVM switch with a Common Access Card (CAC) port. The P784-010 features 24-pin dual-link DVI-I, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The U022-010 is a USB cable that connects to the KVM's CAC port for accessing smart cards, scanners and biometric readers, including fingerprint readers, to bolster security.

Specifically Designed for Select KVMs to Save You Time and Money Recommended for the B002-DV1AC4 or B002-DV1AC8 NIAP KVM, the DVI cable supports video resolutions up to 2560 x 1600 (including 1080p) at 60 Hz. The USB cables also support USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and costs.

Highlights

- Cuts cable clutter and saves money by combining essential KVM cables into just 2
- 10-ft. (3.05 m) 3-in-1 DVI, USB A/B and 3.5 mm audio cable connects KVM to your computer
- Delivers HD picture quality at resolutions up to 2560 x 1600 (1080p) @ 60 Hz
- 10-ft. (3.05 m) USB A/B cable included for KVM's CAC port (smart cards, scanners, etc.)
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a headless computer to a Tripp Lite KVM switch with CAC support
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 10 ft.

System Requirements

- B002-DV1AC4 or B002-DV1AC8 NIAP KVM or other compatible KVM switch

Package Includes

- P784-010 DVI KVM cable kit, 3 in 1 (M/M), 10 ft.
- U022-010 USB A/B cable (M/M), 10 ft.

Specifications

OVERVIEW	
UPC Code	037332243805
Accessory Type	Cable Kit
Technology	DVI; USB 2.0 (High Speed)
Accessory Class	KVM Switch Accessories
VIDEO	
Max Supported Video Resolution	2560 x 1600P @ 60 Hz



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB A (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	3.5MM (MALE); DVI-I DUAL LINK (MALE); USB B (MALE)
Side B - Connector 2	USB B (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Weight (kg)	0.70
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	0 ~ 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.