

DisplayPort KVM Cable Kit for Tripp Lite B005-DPUA2-K and B005-DPUA4 KVM, 4K DP, USB 3.2, 3.5 mm, 6 ft.

MODEL NUMBER: P785-DPKIT06



Convenient cable kit connects a computer or server with DisplayPort, USB and/or 3.5 mm ports to a compatible Tripp Lite KVM switch.

Features

6 ft. Cables Connect Your Computer's DisplayPort, USB and Audio Ports to a Tripp Lite KVM Switch This DisplayPort cable kit includes four cables for connecting your computer to a KVM switch. Recommended for the Tripp Lite B005-DPUA2-K and B005-DPUA4 KVM switches, the kit saves you money by combining necessary cables into one convenient bunch.

DisplayPort The DisplayPort cable lets you view the video content of your computer via the console's connected monitor. It supports Ultra HD True 4K video resolutions up to 4096 x 2160 (4K x 2K) at 60 Hz.

Latching Connectors Help Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean costly and time-consuming signal loss. The latching DisplayPort connectors help you avoid such danger, protecting your audio/video transmission by maintaining a secure link without failure. The latching cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the cord always stays connected.

USB The USB cable connects the KVM switch's USB-B port to your computer's USB-A port. It enables you to control all connected computers from one centralized keyboard/mouse, while also accessing external flash drives, printers, scanners or other devices connected to the switch's USB peripheral ports. The cable supports USB 3.2 Gen 1 data transfer speeds up to 5 Gbps.

3.5 mm Audio Two 3.5 mm stereo cables connect external multimedia speakers, a microphone or headphones.

Quality Construction Provides Superior Signal Transfer Integral strain relief gives the cables extra flexibility, reduces stress and helps the cables move freely without cracking or breaking loose from the connectors. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data.

Highlights

- Includes 6 ft. DisplayPort, USB 3.2 Gen 1 A/B and two 3.5 mm stereo audio cables in one kit
- Supports Ultra HD resolutions up to true 4K @ 60 Hz for crystal-clear video
- Latching DisplayPort plugs maintain constant A/V signal without accidental disconnections
- Supports USB 3.2 Gen 1 data transfer speeds up to 5 Gbps (10x faster than USB 2.0)
- For use with Tripp Lite's B005-DPUA2-K and B005-DPUA4 KVM switches

Applications

- Connect a computer and audio equipment, such as speakers and a microphone, to your Tripp Lite KVM switch

System Requirements

- Computer with USB, DisplayPort and/or 3.5 mm ports
- Tripp Lite B005-DPUA2-K or B005-DPUA4 KVM switch

Package Includes

- P580-006 DisplayPort cable (M/M), 6 ft.
- U322-006 USB-A to USB-B cable (M/M), 6 ft.
- (2) P312-006 3.5 mm audio cables (M/M), 6 ft.

Specifications



OVERVIEW	
UPC Code	037332257024
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	USB: 4.8MM; AUDIO: 3.0MM; DISPLAYPORT: 6.5MM
Color	Black; Blue
Material of Construction	PVC
Wire Gauge (AWG)	USB: 30/28; AUDIO: 28; DISPLAYPORT: 30
ENVIRONMENTAL	
Operating Temperature Range	14 TO 122 F (-10 TO 50 C)
Storage Temperature Range	5 TO 140 F (-15 TO 60 C)
Operating Humidity Range	0 TO 90% RH, Non-Condensing
Storage Humidity Range	0 TO 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side A - Connector 2	USB 3.0 A (MALE)
Side A - Connector 3	(2) 3.5MM (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 2	USB 3.0 B (MALE)
Side B - Connector 3	(2) 3.5MM (MALE)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	4096 x 2160 @ 60 Hz
Displayport Specification	1.2
HDCP Specification	2.2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	Stereo Audio
Max Supported Color Depth	24-bit True Color



Technology	DisplayPort; Stereo Audio; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
Chroma Sub Sampling	4:4:4
SPECIAL FEATURES	
HDR Support	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>