



Powering Business Worldwide

10-ft. Universal File Transfer Serial Gold Cable (DB9F-25F/DB9F-25F)

MODEL NUMBER: P806-010-R



Highlights

- Gold-plated connectors provide superior conductivity
- Retail packaging

System Requirements

- Two computers with serial ports (DB9 or DB25)
- File Transfer Software

Package Includes

- 10-ft. Univ File Transfer Serial File Transfer Cable DB9F and DB25F to DB9F and DB25F Gold Connectors

Description

Tripp Lite's universal interlink serial cable is used to transfer files between computers. This 10-ft cable features both a DB9F and a DB25F gold connector on each end. Gold plated connectors and gold plated copper contacts offer superior conductivity. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Retail clamshell packaging.

Features

- Connects two computers together via their serial ports for file transferring purposes.
- Universal cable - Can be used with any two serial ports, no matter which connector type (DB9 or DB25)
- Superior molded design with ergonomic thumbscrews strain relief and durable PVC pre-mold and cable jacket
- 10-ft. universal cable
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Features gold-plated connectors for superior conductivity and support of high-speed applications
- Connectors: DB9 female and DB25 female to DB9 female and DB25 female
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
UPC Code	037332014597
CONNECTIONS	
Side A - Connector 1	DB9/DB25 (FEMALE)
Side B - Connector 1	DB9/DB25 (FEMALE)
PHYSICAL	



Powering Business Worldwide

Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	7.25 x 7.00 x 2.25
Shipping Dimensions (hwd / cm)	18.42 x 17.78 x 5.72
Shipping Weight (lbs.)	0.84
Shipping Weight (kg)	0.38
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.