

## Serial ATA (SATA) Right-Angle Signal Cable (7Pin/7Pin-Up), 12-in. (30.48 cm)

MODEL NUMBER: P941-12I



### Features

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Features 7Pin Straight and 7Pin Right-Angle Up connectors
- Angled connector ideal for situations in which space is at a premium, and reduces stress / excessive bending on the cable
- SATA III (6Gbps) / SATA II (3Gbps) / SATA I (1.5Gbps) Compliant
- Cable is shielded to protect against EMI/RFI

### Highlights

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Features 7Pin Straight and 7Pin Right-Angle Up connectors
- Angled connector ideal for situations in which space is at a premium, and reduces stress / excessive bending on the cable
- SATA III (6Gbps) / SATA II (3Gbps) / SATA I (1.5Gbps) Compliant
- Cable is shielded to protect against EMI/RFI

### Applications

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Compatible with Serial ATA Hard Drives, Blu-ray/DVD/CD Drives and other Serial ATA devices

### System Requirements

- SATA device
- SATA controller
- Data transfer rates are dependent upon the version of SATA supported by your device and controller

### Package Includes

- Serial ATA (SATA) Right Angle Signal Cable (7Pin/7Pin-Up) 12-in.

## Specifications

| OVERVIEW             |                                    |
|----------------------|------------------------------------|
| UPC Code             | 037332184399                       |
| Technology           | SATA/eSATA                         |
| CONNECTIONS          |                                    |
| Side A - Connector 1 | 7 PIN SATA STRAIGHT (MALE)         |
| Side B - Connector 1 | 7 PIN SATA (MALE) - RIGHT ANGLE UP |
| PHYSICAL             |                                    |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                           |
|-------------------------------------|---------------------------|
| Color                               | Red                       |
| Cable Jacket Color                  | Red                       |
| Cable Outer Diameter (OD)           | 2.2 +/- 0.10 mm           |
| Cable Length (ft.)                  | 1                         |
| Cable Length (m)                    | 0.30                      |
| Cable Length (in.)                  | 12                        |
| Cable Length (cm)                   | 30.48                     |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50        |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27      |
| Shipping Weight (lbs.)              | 0.04                      |
| Shipping Weight (kg)                | 0.02                      |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Product Compliance                  | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.