

Serial ATA (SATA) Right-Angle Signal Cable (7Pin/7Pin-Up), 19-in. (48.26 cm)

MODEL NUMBER: P941-19I



Features

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Support data transfer rates of up to 6.0 Gbps
- Narrow cables design: 1) simplifies cable routing and installation 2) improves air flow within CPU (no more big ribbons blocking air movement)3) right-angle design for tight spaces
- Meets Serial ATA 1.0 standards, including Errata 029
- Cable is shielded to protect against EMI/RFI

Highlights

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Features 7Pin Straight and 7Pin Right-Angle Up connectors
- Angled connector ideal for situations in which space is at a premium, and reduces stress / excessive bending on the cable
- SATA III (6Gbps) / SATA II (3Gbps) / SATA I (1.5Gbps) Compliant
- Cable is shielded to protect against EMI/RFI

Applications

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Compatible with Serial ATA Hard Drives, Blu-ray/DVD/CD Drives and other Serial ATA devices

System Requirements

- Serial ATA device
- Serial ATA controller

Package Includes

- 19-in. Serial ATA Right Angle (SATA) Signal Cable 7Pin/7Pin, Straight/Up

Specifications

OVERVIEW	
UPC Code	037332120069
Technology	SATA/eSATA
PHYSICAL	
Color	Red
Cable Jacket Color	Red
Wire Gauge (AWG)	26
Cable Length (ft.)	1.6
Cable Length (m)	0.49

Cable Length (in.)	19
Cable Length (cm)	48.26
Shipping Dimensions (hwd / in.)	5.31 x 3.94 x 0.50
Shipping Dimensions (hwd / cm)	13.49 x 10.01 x 1.27
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
CONNECTIONS	
Side A - Connector 1	7 PIN SATA (MALE)
Side B - Connector 1	7 PIN SATA (MALE) - RIGHT ANGLE UP
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty