

Serial ATA (SATA) Right-Angle Signal Cable (7Pin/7Pin-Down), 19-in.

MODEL NUMBER: P942-19I



Description

Tripp Lite expands its line of hard drive cables with the introduction of our new line of serial ATA cables. The signal cables connect any high speed Serial ATA device to a Serial ATA controller. Serial ATA delivers two significant benefits: it support much higher data transfer rates (up to 6.0 Gbps...backward compatible to 1.5Gbps) and the narrow cable design helps improve internal air flow. Perfect for the desktop or server that has multiple drives. These cables feature 7-pin straight/7-pin right-angle key down connectors and offer easy installation.

Features

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Support data transfer rates of up to 6.0 Gbps
- Narrow cables design: 1) simplifies cable routing and installation 2) improves air flow within CPU (no more big ribbons blocking air movement)
- Meets Serial ATA 1.0 standards, including Errata 029
- Cable is shielded to protect against EMI/RFI

Highlights

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Features 7Pin Straight and 7Pin Right-Angle Down connectors
- Angled connector ideal for situations in which space is at a premium, and reduces stress / excessive bending on the cable
- SATA III (6Gbps) / SATA II (3Gbps) / SATA I (1.5Gbps) Compliant
- Cable is shielded to protect against EMI/RFI

Applications

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Compatible with Serial ATA Hard Drives, Blu-ray/DVD/CD Drives and other Serial ATA devices

System Requirements

- Serial ATA device
- Serial ATA controller

Package Includes

- 19-in. Serial ATA Right Angle (SATA) Signal Cable 7Pin/7Pin, Straight/Down

Specifications

OVERVIEW	
UPC Code	037332120076
Technology	SATA/eSATA



INPUT	
Cable Length (ft.)	1.6
Cable Length (m)	0.5
Cable Length (in.)	19
Cable Length (cm)	48.26
PHYSICAL	
Color	Red
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.14
Wire Gauge (AWG)	26
CONNECTIONS	
Side A - Connector 1	7 PIN SATA (MALE)
Side B - Connector 1	7 PIN SATA (MALE) - RIGHT ANGLE DOWN
STANDARDS & COMPLIANCE	
Certifications	RoHS-Compliant
NOM (Mexico)	N
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>