

## eSATA, SATA-II External Signal Shielded Cable (7Pin/7Pin), 2M (6.56 ft.)

MODEL NUMBER: P950-02M



### Highlights

- Connect your high-speed eSATA device to a eSATA controller
- Support data transfer rates of up to 6Gbps
- Cable is double-shielded to protect against EMI/RFI

### System Requirements

- eSATA Device
- eSATA Controller

### Package Includes

- 2 Meter ( 6ft ) eSATA (SATA-II) External Signal Cable (7Pin/7Pin)

### Features

- Connect your high-speed eSATA device to an eSATA controller
- Support data transfer rates of up to 6Gbps
- 2 Meter ( 6ft ) Cable is double-shielded to protect against EMI/RFI
- RoHS Compliant

## Specifications

OVERVIEW	
UPC Code	037332153869
Technology	SATA/eSATA
CONNECTIONS	
Side A - Connector 1	7 PIN ESATA (MALE)
Side B - Connector 1	7 PIN ESATA (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6.6
Cable Length (m)	2.01
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.