

eSATA, SATA-II External Signal Shielded Cable (7Pin/7Pin), 36-in. (91.44 cm)

MODEL NUMBER: P950-36I



Highlights

- Connect your high-speed eSATA device to a eSATA controller
- Support data transfer rates of up to 6Gbps
- Cable is double-shielded to protect against EMI/RFI

System Requirements

- eSATA Device
- eSATA Controller

Package Includes

36inch (3ft) eSATA (SATA-II)
External Signal Cable (7Pin/7Pin)

Features

- Connect your high-speed eSATA device to an eSATA controller
- Support data transfer rates of up to 6 Gbps
- 36" Cable is double-shielded to protect against EMI/RFI
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332130969
Technology	SATA/eSATA
CONNECTIONS	
Side A - Connector 1	7 PIN ESATA (MALE)
Side B - Connector 1	7 PIN ESATA (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Cable Length (cm)	91.44



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.