

SATA to eSATA Transition Cable (7Pin/7Pin), 18-in. (45.72 cm)

MODEL NUMBER: P952-18I



Connects newer eSATA devices to older SATA ports without the expense and effort of installing an internal adapter.

Features

18 in. Transition Cable Connects New eSATA Devices to Older SATA PortsOptimized for data storage, the P952-18I SATA to eSATA cable allows you to connect newer eSATA devices to older SATA ports without the added time and expense of installing an internal adapter in your computer. This red transition cable has 7-pin male connectors on both ends and provides data transfer rates up to 6 Gbps for fast file uploads and downloads. The 18-inch length helps reduce cable clutter.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform BetterVarious electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This cable is fully shielded against disruptive line noise that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Specifications

OVERVIEW	
UPC Code	037332140630
Technology	SATA/eSATA
CONNECTIONS	
Side A - Connector 1	7 PIN SATA (MALE)
Side B - Connector 1	7 PIN ESATA (MALE)
PHYSICAL	
Color	Red

Highlights

- Connects newer eSATA devices to older SATA ports with no internal adapter needed
- Transfers data at speeds up to 6 Gbps for fast file uploads and downloads
- Fully shielded against EMI/RFI interference to help connected devices last longer
- 18 in. length allows flexibility in placing devices, while avoiding cable clutter
- Plug-and-play operation makes it easy to connect in seconds

Applications

- Connect a newer eSATA device to an older SATA port without installing an internal adapter
- Transfer data from one drive to another at speeds up to 6 Gbps

Package Includes

- P952-18I SATA to eSATA Transition Cable (7Pin/7Pin), 18 in.



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Color	Red
Cable Length (ft.)	1.5
Cable Length (m)	0.46
Cable Length (in.)	18
Cable Length (cm)	45.72
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.50
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 24.13
Shipping Weight (lbs.)	0.12
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	0.500 x 7.000 x 9.500
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 149°F (-20° to 65°C)
Operating Humidity Range	20 to 80%
Storage Humidity Range	10 to 90%
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.