

Power Distribution Unit (PDU) - Accessory adds additional outlet types to dual voltage UPS System

MODEL NUMBER: PDU6K

Description

Tripp Lite's PDU6K AC power distribution unit offers 24 amp, 240/120V capacity in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for wallmount, under-counter or 2U rackmount installation. Detachable flanges allow user configuration in dozens of potential mounting schemes. Includes 8 outlets total (1xL5-30R, 1xL5-20R, 2xL6-30R, 2xL6-20R, 1x6-20R), with NEMA L14-30P input plug. 4 ft. AC input cord.

PLUG/OUTLETS: Input: NEMA L14-30P/Output: 1 L5-30, 1 L5-20, 2 L6-30, 2 L6-20, 2 6-20R

ELECTRICAL: 240V AC input, 240/120V AC output

FORMAT: Supports 19 in. rackmount (2U), wallmount and under-counter

Features

- · Corded AC power distribution unit with 8 output receptacles
- Versatile all-metal cabinet with detachable mounting flanges allows wallmount, under-counter and 19 inch rackmount mounting in 2U format
- 4 120V and 4 240V output receptacles (1xL5-30R, 1xL5-20R, 2xL6-30R, 2xL6-20R, 1x6-20R)
- 4 ft. AC cord with L14-30 plug-in connection
- Removable plug enables hardwire input connection

Highlights

- 8 outlet PDU system adds 240 and 120V output receptacles to select dual voltage 240/120V UPS systems
- Includes 4 ft. cord with L14-30 plug
- Input plug supports hardwire input connection
- Supports installation in 2U rackmount, wallmount and under-counter applications

Package Includes

- PDU6K rackmount power strip
- Instruction manual

Specifications

OVERVIEW		
OVERVIEW		
UPC Code	037332119346	
INPUT		
INPUT		
Input Phase	Single-Phase	
Input Connection Type	Nema L14-30 input plug, removable for 4 wire hardwire installation	
PDU Plug Type	Hardwire	
Voltage Compatibility (VAC)	240	
Input Cord Length (ft.)	4	
Input Cord Length (m)	1.22	
OUTPUT		
Output Receptacles	(1) 6-15/20R; (1) L5-20R; (1) L5-30R; (2) L6-20R; (1) L6-30R	
Circuit Breaker (amps)	20	
Overload Protection	20A resettable double pole breaker	
PHYSICAL		
Material of Construction	Metal	



Power Cord Color	Black
Form Factors Supported	2U rackmount, wallmount, under-counter
Housing Color	Black
Included Mounting Accessories	Recessed rackmount installation brackets
PDU Form Factor	Horizontal (2U)
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	6.50 x 18.25 x 8.25
Shipping Dimensions (hwd / cm)	16.51 x 46.36 x 20.96
Shipping Weight (lbs.)	8.00
Shipping Weight (kg)	3.63
Unit Dimensions (hwd / in.)	3.500 x 17.250 x 3.750
Unit Dimensions (hwd / cm)	8.9 x 43.8 x 9.5
Unit Weight (lbs.)	6.25
Unit Weight (kg)	2.83

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.