

1.5kW Single-Phase Local Metered PDU, 100-127V Outlets (13 5-15R), 5-15P, 100-127V Input, 15 ft. (4.57 m) Cord, 1U Rack-Mount

MODEL NUMBER: PDUMH15-RA



Highlights

- Local metered single phase 12A 100-127V PDU
- 1U horizontal rackmount, Digital current meter
- NEMA 5-15P input with 15-ft. (4.57 m) line cord
- 13 NEMA 5-15R outlets oriented with ground pin on the bottom (1 front / 12 rear)
- Reversible housing 4.5 in / 11.4cm depth

Package Includes

- PDUMH15-RA Local Metered rackmount PDU
- Owner's manual with warranty information

Features

- 15A single phase 100-127V Local Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- Attached NEMA 5-15P 15A 100-120V input plug with 15-ft. (4.57 m) line cord
- 1U horizontal rackmount format installs in one rack space
- 13 NEMA 5-15R outlets oriented with the ground pin on the bottom (1 front facing / 12 rear)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug

Specifications

OVERVIEW	
UPC Code	037332183231
PDU Type	Local Metered
INPUT	
PDU Input Voltage	100; 120; 125; 127
Recommended Electrical Service	Single-phase 15A 100-127V service
Maximum Input Amps	12

Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 12A total capacity; 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(13) 5-15R
Output Nominal Voltage	100-127V
Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Metal
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
Minimum Required Rack Depth (cm)	17.27
Minimum Required Rack Depth (inches)	6.8
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / in.)	2.25 x 20.50 x 10.00
Shipping Dimensions (hwd / cm)	5.72 x 52.07 x 25.40
Shipping Weight (lbs.)	5.20
Shipping Weight (kg)	2.36
Unit Dimensions (hwd / in.)	1.750 x 17.300 x 3.750
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 9.5
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)

Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
FEATURES & SPECIFICATIONS	
TVSS Grounding	Rear grounding lug
STANDARDS & COMPLIANCE	
Product Certifications	RETIE (Colombia); NOM (Mexico); UL 60950-1
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty