

1.9kW Single-Phase Metered Automatic Transfer Switch PDU, 2 120V L5-20P / 5-20P Inputs, 16 5-15/20R Outputs, 1U, TAA

MODEL NUMBER: PDUMH20AT



Description

Tripp Lite's Metered Automatic Transfer Switch / ATS PDU provides a redundant power option for single-corded network devices. Dual input cords support separate connection to PRIMARY and SECONDARY power sources. The ATS will normally maintain continuous output to all outlets as derived from the primary input cable. If the primary power source becomes unstable or fails altogether, the ATS will switch over to the secondary power source until the primary input is restored and stable. Super-fast switchover between primary and secondary power sources occurs within milliseconds. ATS functionality is supported by any two compatible AC power sources, regardless of phase angle, to support a variety of advanced redundant power networking applications. Enables fault tolerant hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system. In a two-UPS environment, the primary input cable must be supported by a full time sine wave UPS with zero transfer time. Tripp Lite SmartOnline series is highly recommended for use as the primary UPS in a two-UPS application. ATS configurations utilizing separate mains circuits, backup generators and even separate utility power grid feeds are fully supported. On-board ATS processor constantly evaluates power quality on both input sources to prevent transfer to the secondary source when unavailable or of lower quality than the primary source. Front input LED's display primary or secondary power availability.

Features

- 120V 20A Automatic Transfer Switch (ATS) / Metered PDU (Agency de-rated to 16A continuous)
- Provides a redundant A/B power option for non-redundant networking equipment with a single input power cord
- Digital display continuously reports total output power consumption in amps
- 1U horizontal rackmount form factor; 14.5 in. / 36.8 cm depth
- 16 built-in NEMA 5-15/20R outlets (8 front / 8 rear)
- Set of two 12 ft. / 3.6m NEMA L5-20P input cables with set of two 5-20P adapters support connection to separate PRIMARY and SECONDARY inputs
- ATS circuits normally maintain output sourced from the primary input cable; As primary input power fails or becomes unstable, the ATS will switch to maintain output sourced from the secondary input cable

Highlights

- Single phase 20A 120V Auto Transfer Switch / ATS PDU
- Enables redundant A/B power option for single-corded network devices
- Separate primary & secondary inputs connect to any two compatible power sources
- 1U horizontal rackmount; 2 NEMA L5-20P / 5-20P inputs; 16 5-15/20R outlets
- Two digit visual current meter reports equipment load in amps; Upgrade options available
- TAA Compliant

Package Includes

- ATS / Metered PDU with attached L5-20P primary input cord
- Detachable C19 to NEMA L5-20P secondary input cord
- Set of two L5-20R to 5-20P plug adapters
- 1U rackmount installation brackets
- User manual with warranty information



until power on the primary input is restored and stable

- ATS configurations enable fault-tolerant, hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system (in a two-UPS environment, the primary input cable must be supported by an online UPS with zero transfer time similar to Tripp Lite SmartOnline series)
- Advanced ATS configurations utilizing separate mains circuits, backup generators and even separate out of phase utility power grid feeds are fully supported
- On-board ATS processor constantly evaluates power quality on both inputs to prevent transfer to the secondary source when unavailable or of lower quality than the primary source
- Super-fast switchover between primary and secondary power sources occurs in 2-7 milliseconds
- Built-in card slot supports optional SNMPWEBCARD or WEBCARDLX for permanent upgrade to a switched & monitored PDU system
- Outlets are factory programmed for sequential turn-on at 250 millisecond intervals when the PDU is first energized to prevent inrush-related equipment interaction on startup
- Front panel LEDs confirm power availability on both input lines
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332126665
PDU Type	Auto-Transfer Switch; Metered
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	20A 120V
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A maximum
PDU Plug Type	(2) NEMA 5-20P; (2) NEMA L5-20P
Input Phase	Single-Phase
Input Cord Details	Set of two L5-20P cordsets with two 5-20P adapters enable connection to separate PRIMARY and SECONDARY power sources
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
OUTPUT	
Output Capacity Details	2.03kW (127V), 1.92kW (120V), 1.6kW (100V) / 20A total capacity (Agency de-rated to 16A); 16A max per outlet
Frequency Compatibility	50 / 60 Hz



Output Receptacles	(16) 5-15/20R
Output Nominal Voltage	100; 120; 127
Overload Protection	n/a
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Front Panel LEDs	16 front panel LEDs display power on / off status for each outlet, plus 2 additional LEDs to indicate input power status for primary and secondary inputs
Switches	n/a
PHYSICAL	
Form Factors Supported	1U rackmount
Material of Construction	Metal
Minimum Required Rack Depth (cm)	49.53
Minimum Required Rack Depth (inches)	19.5
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	13.72 x 59.18 x 51.05
Shipping Dimensions (hwd / in.)	5.40 x 23.30 x 20.10
Shipping Weight (kg)	9.39
Shipping Weight (lbs.)	20.70
Unit Dimensions (hwd / cm)	4.44 x 44.4 x 36.8
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 14.5
Unit Weight (kg)	5.53
Unit Weight (lbs.)	12.2
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
COMMUNICATIONS	
Network Management Cards	 SNMPWEBCARD ; WEBCARDLX
SNMP Compatibility	Includes slot for optional SNMPWEBCARD or WEBCARDLX accessory to add built-in network interface and enable remote individual outlet control over IP



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SPECIAL FEATURES	
TVSS Grounding	Rear grounding lug
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1 (USA), CSA (Canada), Class A (Emissions), NOM (Mexico), RoHS Compliant, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>