

## 1.4kW Single-Phase Metered PDU, 120V Outlets (8 5-15R), 5-15P, 15ft Cord, 0U Vertical, 24 in.

MODEL NUMBER: PDUMV15-24



### Description

Tripp Lite single phase Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital display. Enables visual monitoring of PDU load levels to prevent overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

### Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA 5-15P 15A 120V input plug with 15ft / 4.5m line cord
- 0U 24in / 61cm vertical rackmount format installs using no rack spaces
- 8 NEMA 5-15R outlets
- Includes 15A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Rear facing installation buttons can be relocated to the left or right surface of the PDU for rear, center or forward-facing outlet orientation in compatible racks
- Included nut and bolt mounting brackets support installation in non button-mount compatible racks, wallmount and raceway applications

## Specifications

### OVERVIEW

### Highlights

- Metered single phase 15A 120V 0U 24in / 61cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15ft / 4.5m cord with NEMA 5-15P input plug
- 8 NEMA 5-15R outlets
- Toolless button mount and bolt-down bracket installation hardware included

### Package Includes

- PDUMV15 Metered Vertical PDU
- Mounting hardware and spare mounting buttons
- Owner's manual with warranty information



UPC Code	037332182852
PDU Type	Metered
<b>INPUT</b>	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
<b>OUTPUT</b>	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Output Nominal Voltage	100; 120; 127
Overload Protection	15A circuit breaker
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with integrated safety cover
<b>PHYSICAL</b>	
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
Material of Construction	Metal
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	4.83 x 13.72 x 68.83
Shipping Dimensions (hwd / in.)	1.90 x 5.40 x 27.10
Shipping Weight (kg)	1.54
Shipping Weight (lbs.)	3.40
Unit Dimensions (hwd / cm)	61 x 4.45 x 3.2
Unit Dimensions (hwd / in.)	24 x 1.75 x 1.25
Unit Weight (kg)	1.20
Unit Weight (lbs.)	2.65



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL60950-1 (USA) and CSA60950-1 (Canada), NOM (Mexico), Class A (Emissions), RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>