

2kW Single-Phase Local Metered PDU, 100-127V Outlets (6 5-15/20R), L5-20P/5-20P adapter, 0U Vertical, 24-in.

MODEL NUMBER: PDUMV20-24



Highlights

- Local Metered single phase 100-127V 16A 0U 24-in. / 61cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA L5-20P plug and 5-20P adapter
- 6 NEMA 5-15/20R outlets
- Toolless button mount and bolt-down bracket installation hardware included

Package Includes

- PDUMV20-24 Local Metered Vertical PDU
- (1) L5-20P to 5-20P plug adapter
- Mounting hardware and spare mounting buttons
- Instruction manual with warranty information

Features

- 20A single phase 100-127V Local Metered Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA L5-20P input plug with 15-ft. (4.57 m) line cord and 5-20P adapter
- 0U 24-in. / 61cm vertical rackmount format installs using no rack spaces
- 6 NEMA 5-15/20R outlets
- Includes 20A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Specifications

OVERVIEW	
UPC Code	037332182845
PDU Type	Local Metered
INPUT	
PDU Input Voltage	100; 120; 125; 127
Recommended Electrical Service	Single-phase 20A 100-127V service
Maximum Input Amps	16
Maximum Input Amps Details	Agency de-rated to 16A continuous

PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	2.03kW (127V), 1.92kW (120V), 1.6kW (100V) / 16A total capacity; 16A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15/20R
Output Nominal Voltage	100-127V
Overload Protection	20A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with integrated transparent safety cover
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Aluminum
Form Factors Supported	Vertical
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	2.20 x 6.20 x 26.50
Shipping Dimensions (hwd / cm)	5.59 x 15.75 x 67.31
Shipping Weight (lbs.)	6.30
Shipping Weight (kg)	2.86
Unit Dimensions (hwd / in.)	24.470 x 1.640 x 1.500
Unit Dimensions (hwd / cm)	62.2 x 4.2 x 3.81
Unit Weight (lbs.)	3.52
Unit Weight (kg)	1.60
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000

Operating Elevation (m)	0-3000
STANDARDS & COMPLIANCE	
Product Certifications	RETIE (Colombia); NOM (Mexico); UL 60950-1
Product Compliance	RoHS; FCC Part 15 Class A (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty