

4-Outlet Power Strip, 10 ft. Cord, NEMA 5-15P Plug, 12 in.

MODEL NUMBER: **PS120410**



Metal 12 in. power strip distributes power to multiple devices in an industrial, office, retail, rackmount, raceway, workbench or point-of-sale setting.

Description

The 12-inch PS120410 4-Outlet Power Strip is an appropriate power distribution solution for powering multiple devices in a home, office, warehouse, workbench, rackmount, raceway, retail display or point-of-sale setting. The long 10-foot power cord with NEMA 5-15P plug lets you mount the power strip away from the power source for maximum convenience and flexibility. Place it on the floor, or use the included hardware to install it vertically or horizontally on a wall, workbench or under a counter.

Four NEMA 5-15R outlets are arranged in standard 1.77-inch center-to-center spacing for easy connection to equipment. A built-in 15A circuit breaker detects dangerous overloads that could damage valuable equipment and immediately shuts down the PS120410. A transparent switch cover protects against accidental shutdowns. A lighted on/off switch confirms at a glance that the power strip is operating.

Features

Ideal Power Distribution

- Recommended for industrial, office, retail, rackmount, raceway, workbench and point-of-sale settings
- 4 NEMA 5-15R outlets with 1.77 in. center-to-center spacing
- 10 ft. power cord with NEMA 5-15P plug
- Meets UL1363 (USA) and cUL (Canada) certifications

Premium Safety Features

- 15A resettable circuit breaker prevents dangerous overloads
- Transparent switch cover eliminates accidental shutdowns

Highlights

- 4 NEMA 5-15R outlets with 1.77 in. center-to-center spacing
- 15A resettable circuit breaker
- Lighted on/off switch with transparent safety cover
- Heavy-duty all-metal housing
- 10 ft. power cord with NEMA 5-15P plug

Package Includes

- PS120410 4-Outlet Power Strip, 10 ft. Cord, 12 in.
- Mounting hardware
- Owner's manual



- Lighted on/off switch confirms operation at a glance

Rugged All-Metal Housing

- 12 in. length
- Hardware included for mounting on a wall, floor, workbench or under a counter

Specifications

OVERVIEW	
UPC Code	037332198525
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
Outlet Spacing	1.77in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Antimicrobial Coating	No
Color	Silver



Color (AC Line Cord)	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Included Mounting Accessories	Includes mounting clips
Integrated Keyhole Mounting Slots	No
Material of Construction	Aluminum
Outlets Measurement (Center to Center)	1.77
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	6.10 x 12.19 x 39.12
Shipping Dimensions (hwd / in.)	2.40 x 4.80 x 15.40
Shipping Weight (kg)	0.95
Shipping Weight (lbs.)	2.10
Unit Dimensions (hwd / cm)	3.18 x 4.12 x 30.48
Unit Dimensions (hwd / in.)	1.25 x 1.62 x 12
Unit Weight (kg)	0.58
Unit Weight (lbs.)	1.28
STANDARDS & COMPLIANCE	
Canada	cUL
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>