

## 4-Outlet Power Strip, 10 ft. (3.05 m) Cord, NEMA 5-15P Plug, 12 in.

MODEL NUMBER: **PS120410**



Metal 12 in. power strip distributes power to multiple devices in an industrial, office, retail, rackmount, raceway, workbench or point-of-sale setting.

### Features

#### Ideal Power Distribution

- Recommended for industrial, office, retail, rackmount, raceway, workbench and point-of-sale settings
- 4 NEMA 5-15R outlets with 1.77 in. center-to-center spacing
- 10-ft. (3.05 m) power cord with NEMA 5-15P plug
- Meets UL1363 (USA) and cUL (Canada) certifications

#### Premium Safety Features

- 15A resettable circuit breaker prevents dangerous overloads
- Transparent switch cover eliminates accidental shutdowns
- Lighted on/off switch confirms operation at a glance

#### Rugged All-Metal Housing

- 12 in. length
- Hardware included for mounting on a wall, floor, workbench or under a counter

## Specifications

OVERVIEW	
UPC Code	037332198525
INPUT	
Nominal Input Voltage(s) Supported	120V AC

### Highlights

- 4 NEMA 5-15R outlets with 1.77 in. center-to-center spacing
- 15A resettable circuit breaker
- Lighted on/off switch with transparent safety cover
- Heavy-duty all-metal housing
- 10-ft. (3.05 m) power cord with NEMA 5-15P plug

### Package Includes

- PS120410 4-Outlet Power Strip, 10-ft. (3.05 m) Cord, 12 in.
- Mounting hardware
- Owner's manual

Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
Outlet Spacing	1.77in.
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
<b>PHYSICAL</b>	
Color	Silver
Material of Construction	Aluminum
Power Cord Color	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Housing Color	Silver
Included Mounting Accessories	Includes mounting clips
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	1.77 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 4.80 x 15.40
Shipping Dimensions (hwd / cm)	6.10 x 12.19 x 39.12
Shipping Weight (lbs.)	2.10
Shipping Weight (kg)	0.95
Unit Dimensions (hwd / in.)	1.250 x 1.620 x 12.000

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Unit Dimensions (hwd / cm)	3.18 x 4.12 x 30.48
Unit Weight (lbs.)	1.28
Unit Weight (kg)	0.58
Outlet Spacing	1.77 in.
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.