

16-Outlet 1U Rack-Mount AC Charger Power Strip, 120V, 15A, 15 ft. (4.57 m) Cord

MODEL NUMBER: PS1916D1U



Charges up to 16 notebooks, netbooks, tablets or other battery-intensive electronic devices that use a NEMA 5-15P power adapter. Can be mounted in 1U of rack space for out-of-the-way convenience.

Description

The PS1916D1U 16-Outlet 1U Rack-Mount AC Charger Power Strip provides high-speed charging for up to 16 mobile devices simultaneously, such as notebooks, netbooks, tablets and other battery-intensive electronics that use a NEMA 5-15P plug.

This power strip features 16 built-in NEMA 5-15R AC outlets attached to convenient dongles that easily accommodate large transformer plugs. It's compatible with all devices that charge via standard AC outlets (such as Chromebooks, MacBook Airs and Ultrabooks) or user-supplied USB power adapters (such as smartphones, iPads, Kindles, Kindle Fires and Surface models).

The all-steel PS1916D1U mounts into 1U of two- or four-post rack space using the included hardware. The NEMA 5-15P input plug is attached to a 15-ft. (4.57 m) power cord long enough to reach a PDU or AC wall outlet. A 15-amp circuit breaker protects against overloads and short circuits. A transparent cover guards the lighted on/off switch from accidental shutdowns.

Features

Charges Up to 16 Electronic Devices at the Same Time

- Compatible with all devices that charge via standard AC outlets, including Chromebooks, MacBook Airs and Ultrabooks
- Compatible with all devices that charge via user-supplied USB adapters, including smartphones, iPads, Kindles, Kindle Fires and Surface tablets
- Convenient dongles easily accommodate large transformer plugs

Keeps Equipment Safe and Secure

- 15A circuit breaker protects against overloads and short circuits
- Transparent cover guards lighted on/off switch from accidental shutdowns

Mounts Easily to Rack

- All-steel unit mounts into 1U of 2- or 4-post rack space
- Mounting hardware included
- 15-ft. (4.57 m) power cord with NEMA 5-15P plug long enough to reach PDU or wall socket

Highlights

- Compatible with devices that charge via AC outlet or USB adapter
- 16 NEMA 5-15R dongles accommodate large transformer plugs
- Heavy-duty steel construction engineered to last
- 15-ft. (4.57 m) AC power cord with NEMA 5-15P input plug
- Ready to mount in 2- or 4-post rack using included hardware

Package Includes

- PS1916D1U 16-Outlet 1U Rack-Mount AC Charger Power Strip
- Mounting hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332188700
Product Type	Power Strip
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC
Input Circuit Breakers	15A circuit breaker
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) 5-15R
Circuit Breaker (amps)	15
Output Nominal Voltage	125V
Transformer Accommodation	(16) Yes
Outlet Details	16 NEMA 5-15R dangle output receptacles
Right-Angle Outlets	Yes
CHARGING	
Number of Charging Ports	16
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(16) 12A

PHYSICAL	
Color	Black
Material of Construction	Metal
Rack Height	1U
Power Cord Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.19 x 15.53 x 20.57
Shipping Dimensions (hwd / cm)	5.56 x 39.45 x 52.25
Shipping Weight (lbs.)	7.29
Shipping Weight (kg)	3.31
Unit Dimensions (hwd / in.)	1.750 x 19.000 x 4.000
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 10.16
Unit Weight (lbs.)	6.44
Unit Weight (kg)	2.92
FEATURES & SPECIFICATIONS	
Grounding Lug	Yes
Antimicrobial	No
IP68 Rated	No
Built-In Circuit Breaker	Yes
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 60950-1 (Canada); NOM (Mexico); UL 60950-1
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty