

## 2-Outlet Power Strip - British BS1363A Outlets, 220-250V AC, 13A, Direct Plug, BS1363A Plug, White

MODEL NUMBER: **PS1B**



2-outlet power strip distributes electricity to home and office electronics, including computers, power tools and appliances.

### Features

**Compact Power Strip Delivers Electricity to 2 Devices at the Same Time** Compatible with standard electrical equipment, this Protect It!® power strip plugs directly into a wall outlet (no cord required). It features two BS1363A outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

**Compact High-Impact Housing Makes Connecting in Tight Spaces Easier** This direct-plug power strip is easy to install in confined spaces, such as behind furniture. One outlet is located on top of the unit, so a connected power cord runs parallel to the wall, allowing you to push furniture against the wall to maximize space.

**Premium Safety Features Designed for Protecting Your Valuable Equipment** An integrated 13A circuit breaker protects all outlets and automatically cuts power if the protection circuit is incapacitated, preventing equipment damage and indicating replacement is required.

### Highlights

- BS1363A outlets distribute power to appliances, tools, lighting and other electronics
- Plugs directly into the wall (no cord required) for easy installation in tight spaces
- 13A circuit breaker shuts down both UK outlets for safety in case of overload

### Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment

### Package Includes

PS1B 2-Outlet Direct-Plug Power Strip, BS1363A Outlets, White

## Specifications

OVERVIEW	
UPC Code	037332251572
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250



Input Plug Type	British
Right-Angle Plug	No
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) British BS 1363A
Circuit Breaker (amps)	13
Right-Angle Outlets	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	No
<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Color	White
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / cm)	5.08 x 11.94 x 7.37
Shipping Dimensions (hwd / in.)	2.00 x 4.70 x 2.90
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.25
Unit Dimensions (hwd / in.)	29.5 x 7.5 x 6.5
Unit Dimensions (hwd / cm)	11.6 x 2.9 x 2.9
Unit Weight (lbs.)	0.81
Unit Weight (kg)	0.37



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Rotatable Outlets	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>