

## 2-Outlet Power Strip - British BS1363A Outlets, 220-250V AC, 13A, Direct Plug, BS1363A Plug, White

MODEL NUMBER: **PS1B**



2-outlet power strip distributes electricity to home and office electronics, including computers, power tools and appliances.

### Features

**Compact Power Strip Delivers Electricity to 2 Devices at the Same Time** Compatible with standard electrical equipment, this Protect It!® power strip plugs directly into a wall outlet (no cord required). It features two BS1363A outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

**Compact High-Impact Housing Makes Connecting in Tight Spaces Easier** This direct-plug power strip is easy to install in confined spaces, such as behind furniture. One outlet is located on top of the unit, so a connected power cord runs parallel to the wall, allowing you to push furniture against the wall to maximize space.

**Premium Safety Features Designed for Protecting Your Valuable Equipment** An integrated 13A circuit breaker protects all outlets and automatically cuts power if the protection circuit is incapacitated, preventing equipment damage and indicating replacement is required.

## Specifications

OVERVIEW	
UPC Code	037332251572
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250

### Highlights

- BS1363A outlets distribute power to appliances, tools, lighting and other electronics
- Plugs directly into the wall (no cord required) for easy installation in tight spaces
- 13A circuit breaker shuts down both UK outlets for safety in case of overload

### Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment

### Package Includes

PS1B 2-Outlet Direct-Plug Power Strip, BS1363A Outlets, White

Input Plug Type	British
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) British BS 1363A
Circuit Breaker (amps)	13
Right-Angle Outlets	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	No
<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Color	White
Material of Construction	Plastic
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.00 x 4.70 x 2.90
Shipping Dimensions (hwd / cm)	5.08 x 11.94 x 7.37
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	2.000 x 2.200 x 2.800
Unit Dimensions (hwd / cm)	11.6 x 2.9 x 2.9
Unit Weight (lbs.)	0.81

# TRIPP-LITE

by **EATON**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Unit Weight (kg)	0.37
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

# TRIPP-LITE

by **EATON**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.