

Power It! 2-Outlet In-Desk Power and Charging Dock - 4x USB-A, USB-B, HDMI, RJ11, RJ45, 10 ft. Cord, Antimicrobial Protection, Black

MODEL NUMBER: PS222DATAM



Installs level with your desktop surface to charge and power multiple devices simultaneously.

Features

Fits into Your Desktop Surface for Reliable Power and Charging

This Power It!® dock is designed for installation in your workspace's level surface, where its ports are within a convenient arm's reach. When not being used to power or charge devices or connect to a telephone or Ethernet network, you can close the flip-top cover flush against the tabletop to save valuable space. To connect devices, simply pop up the secure cover. This In-Desk Power and Charging Dock is ideal for home and office workstations with limited desk space.

A Variety of Ports and Outlets Accept a Wide Range of Electronic Devices

Two NEMA 5-15R outlets and two USB-A ports (4.5A combined) are available for powering and charging your laptop, tablet, smartphone or other devices. The PS222DATAM also features two USB-A data ports for transferring images, documents and other files, as well as ports for connecting HDMI, USB-B, telephone and Ethernet devices. The 10-foot (3-meter) input cord connects to a compatible AC wall outlet.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Environment

The PS222DATAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Specifications

OVERVIEW	
UPC Code	037332271891
Device Compatibility	Amazon Kindle; Laptop; Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC

Highlights

- Installs flush with your tabletop surface to save space and offer easy access
- 2 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 2 USB-A ports share 4.5A for fast charging of phones and other mobile devices
- HDMI, USB-B, RJ11, RJ45 and 2 USB-A data ports connect a wide range of devices
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- PS222DATAM 2-Outlet In-Desk Power and Charging Dock
- Owner's manual

Recommended Electrical Service	120V
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	No
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	2
Total Charging Amps	4.5A
Total Charging Watts	22.5
Charging Method	USB
Charging Port Type	(2) USB A (FEMALE)
Charging Ports / Amps	(1) 2.1A; (1) 2.4A
Charging Amps per Port	(1) 2.4A; (1) 2.1A
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Plastic

Power Cord Color	Black
Mounting Location	Desktop
Housing Color	Black
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	9.06 x 6.30 x 4.72
Shipping Weight (kg)	1.05
Unit Dimensions (hwd / in.)	8.760 x 5.930 x 3.670
Unit Dimensions (hwd / cm)	8.76 x 5.93 x 3.67
Unit Weight (lbs.)	2.09
Unit Weight (kg)	0.95
Input Cord Color	Black
Mounting Details	Cut 7.95" (201.93 mm) x 4.06" (103.13 mm) hole for installation
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side A - Connector 2	(2) USB B (FEMALE)
Side A - Connector 3	HDMI (FEMALE)
Side A - Connector 4	RJ11 (FEMALE)
Side B - Connector 1	(2) NEMA 5-15R
Side B - Connector 2	(4) USB A (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
Side B - Connector 4	RJ11 (FEMALE)
Side B - Connector 5	RJ45 (FEMALE)
Side A - Connector 5	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	No
Network Speed Support	1 Gbps (Gigabit)
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 308 (Canada); ICES (Canada); NOM (Mexico); UL 962A; UL Listed; cUL Listed
Product Compliance	FCC Part 15 Class B (USA); RoHS
WARRANTY & SUPPORT	



1000 Eaton Boulevard
Cleveland, OH 44122
United States

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.