

4-Outlet Power Strip, Right-Angle NEMA 5-15R - 15A, 120V, 6 ft. (1.83 m) Cord, Right-Angle 5-15P Plug, 24 in.

MODEL NUMBER: PS2404RA06B



4-outlet power strip distributes electricity to rack-mount, raceway or workbench applications in a convenient 24 in. mountable setting.

Features

24 in. Power Strip Delivers Electricity to 4 Devices at the Same Time Compatible with all standard electrical equipment, this reliable power strip features four NEMA 5-15R right-angle outlets that prevent connected power cords from blocking access. The black 24-inch housing spaces the outlets far enough apart to allow plenty of room for bulky transformers and AC adapters without blocking adjacent outlets. Made from rugged extruded aluminum, the PS2404RA06B is designed to endure in demanding network, laboratory or factory environments.

Right-Angle NEMA 5-15P Plug Makes Connecting in Tight Spaces Easier The power strip is easy to install in confined spaces, such as the back of a rack enclosure cabinet or behind furniture. When plugged in, the space-saving right-angle NEMA 5-15P plug guides the 6-ft. (1.83 m) power cord parallel to the AC outlet, allowing you to push furniture against a wall to maximize space. The long cord gives you flexibility in placing the strip away from the outlet where power is most needed.

Vertical or Horizontal Mounting for Racks, Raceways and Workbenches Hardware is included for mounting the 4-outlet power strip either horizontally along a raceway or workbench or vertically in an EIA-standard 19-inch rack. It's an ideal power strip for office, network, workbench, industrial, retail, telecom or other environments in which multi-outlet power distribution is desired.

Premium Safety Features Designed for Protecting Your Valuable Equipment The UL-listed power strip features a lighted on/off switch that provides one-touch control over all connected devices. A transparent cover protects the switch from being turned off accidentally. The built-in 15-amp circuit breaker immediately shuts down the power strip in case of an overload to prevent equipment damage.

Lifetime Warranty The PS2404RA06B is backed by a lifetime warranty, ensuring reliability and performance.

Highlights

- 4 right-angle 5-15R outlets for powering multiple devices in a rack or workbench
- Right-angle 5-15P plug permits easier connection in confined or hard-to-reach spaces
- 6-ft. (1.83 m) cord allows flexibility in placing power strip in relationship to AC outlet
- Metal 24 in. housing designed to stand up in demanding lab and factory environments
- Hardware included for horizontal raceway or vertical rack mounting

Applications

- Distribute power to computer equipment and other devices in an office, network, workbench, industrial, retail or telecom environment

Package Includes

- PS2404RA06B 4-Outlet Power Strip, Right-Angle NEMA 5-15R - 6-ft. (1.83 m) Cord
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332224637



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Color (AC Line Cord)	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Included Mounting Accessories	Includes mounting clips
Integrated Keyhole Mounting Slots	No
Material of Construction	Aluminum
Outlets Measurement (Center to Center)	5.67 in.
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	8.71 x 71.40 x 6.20
Shipping Dimensions (hwd / in.)	3.43 x 28.11 x 2.44
Shipping Weight (kg)	0.98



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	2.16
Unit Dimensions (hwd / cm)	61 x 3.8 x 4.1
Unit Dimensions (hwd / in.)	24 x 1.25 x 1.6
Unit Weight (kg)	0.79
Unit Weight (lbs.)	1.74
STANDARDS & COMPLIANCE	
Canada	cUL
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>