

## 8 Right-Angle Outlet Vertical Power Strip, 120V, 15A, 15 ft. (4.57 m) Cord, 5-15P, 24 in.

MODEL NUMBER: PS2408RA



The PS2408RA power strip provides horizontal or vertical power distribution for rack-mount, raceway and workbench applications in a convenient 24-inch mountable housing.

### Description

The PS2408RA provides a 15-amp, 120v power strip with 8 right-angle NEMA 5-15R receptacles in a rugged, all-metal, mountable housing. It allows for both vertical and horizontal mounting, making it ideal for a variety of uses including office, rack-mount, workbench, industrial and telecom applications. With a right angle NEMA 5-15P plug and 15-ft. (4.57 m) power cord, you don't have to install the PS2408RA next to outlets you already have; it can be mounted across the room and deliver reliable service where you need it most. A lighted and covered On/Off switch helps prevent accidental shut-offs, while a 15-amp circuit breaker guards against dangerous circuit overloads. Its sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

### Features

**Multi-Outlet Power Distribution**

**Vertical or Horizontal Moun**

**Extra Long Power Cord**

**Premium Safety Features**

**Heavy-Duty Housing**

### Specifications

OVERVIEW	
UPC Code	037332187451

### Highlights

- Ideal for applications needing multiple convenience outlets for powering a variety of electronic equipment
- 24-in mountable housing with 8 right-angle NEMA 5-15R receptacles, right-angle plug and a 15-ft. (4.57 m) power cord
- Lighted, covered On/Off switch and 15-amp circuit breaker
- Sturdy construction and heavy-duty, all-metal housing

### Package Includes

- PS2408RA Power Strip
- Mounting hardware
- Instruction manual

<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(8) Yes
Right-Angle Outlets	Yes
Outlet Spacing	2.48 in.
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
<b>PHYSICAL</b>	
Color	Silver
Material of Construction	Aluminum
Power Cord Color	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Housing Color	Silver
Included Mounting Accessories	Includes mounting clips
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	63mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 4.61 x 28.19
Shipping Dimensions (hwd / cm)	6.10 x 11.71 x 71.60

Shipping Weight (lbs.)	3.14
Shipping Weight (kg)	1.42
Unit Dimensions (hwd / in.)	1.250 x 1.680 x 24.520
Unit Dimensions (hwd / cm)	3.18 x 4.27 x 62.29
Unit Weight (lbs.)	2.71
Unit Weight (kg)	1.23
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty