

# Safe-IT 32W 2-Outlet Power Strip - 5-15R Outlets, 3 USB Ports, 6 ft. (1.8 m) Cord, Antimicrobial Protection, White

MODEL NUMBER: **PS26PD32WCAM**



### Highlights

- 2 NEMA 5-15R outlets are spaced apart to accommodate bulky transformers
- 2 USB-A ports share 4.8A for fast charging of phones, tablets and other mobile devices
- USB-C PD 3.0 charging port delivers 20W of charging power for laptops
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

### Package Includes

- PS26PD32WCAM 2-Outlet Power Strip
- Owner's manual

Safely charges and powers up to 5 devices, including laptops and tablets, during important workplace meetings and conferences.

### Features

#### 2-Outlet Power Strip Safeguards Your Sensitive Electronics

Ideal for your home or office workstation or travel use, the PS26PD32WCAM features two NEMA 5-15R outlets for plugging in your laptop, printer, external hard drive or other conference-table electronics. The outlets are located on opposite edges to accept bulky transformers without blocking any outlets or ports.

#### USB Ports Allow Safe and Rapid Charging

Two USB-A ports are available for charging your smartphones, tablets and other USB mobile devices. They share 4.8A of charging power, which is plenty for delivering ample power to demanding devices. A USB-C PD 3.0 port delivers 20W of charging power for laptops and other larger devices. All three ports share 32W maximum.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT™ PS26PD32WCAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

#### Compact Round Design Gives You Plenty of Options for Installation and Use

Less than four inches in width, the PS26PD32WCAM fits easily into your home or office workspace, providing power and USB charging at your fingertips. Its compact design also makes the power strip ideal for travel, fitting easily into your backpack, laptop bag or suitcase for use in hotels, conference rooms and cruise ships. The six-foot (1.8-meter) braided power cord connects to an AC wall outlet.

## Specifications

OVERVIEW	
UPC Code	037332274892
Device Compatibility	Laptop; Phone; Tablet



Powering Business Worldwide



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Gauge Type	16 gauge
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	10
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
CHARGING	
Number of Charging Ports	3
Total Charging Watts	32
Charging Method	USB
Charging Port Type	(2) USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports Details	2 x USB-A (2.4A) charging ports for phones, laptops, and other devices1 x USB-C (3A) PD charging port for fast charging
Charging Ports / Amps	(1) 3A / 2A / 1.5A; (2) 4.8A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No



Powering Business Worldwide



PHYSICAL	
Material of Construction	Plastic
Plug Color	White
Power Cord Jacket Type	Braided
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	2.60 x 4.40 x 6.70
Shipping Dimensions (hwd / cm)	6.60 x 11.18 x 17.02
Shipping Weight (lbs.)	1.10
Shipping Weight (kg)	0.50
Unit Dimensions (hwd / in.)	3.110 x 3.860 x 1.350
Unit Dimensions (hwd / cm)	7.9 x 9.8 x 3.4
Unit Weight (lbs.)	0.82
Unit Weight (kg)	0.37
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 21 (Canada); ICES (Canada); UL 817
Product Compliance	FCC Part 15 Class B (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.