


## 12-Outlet Vertical Power Strip, 120V, 15A, 15-ft. Cord, 5-15P, 36 in.

MODEL NUMBER: **PS3612**



### Highlights

- 12 outlets
- Convenient and safe covered, on/off switch
- 15-amp circuit breaker
- 15-ft. cord
- 36" length

### Package Includes

- PS3612
- Mounting hardware
- Instruction manual

### Description

Tripp Lite's PS3612 power strip offers 15 amp, 120V multi-outlet AC power distribution in a convenient 36 inch mountable housing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications. Includes 12 NEMA 5-15R output receptacles with 2.638 inch center-to-center spacing, 15 ft AC line cord and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 12 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: 36 in. corded, mountable power strip

### Features

- Sturdy all-metal 36 inch corded strip format with 2.638 inch center-to-center outlet spacing
- Includes 12 NEMA 5-15R output receptacles
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- Lighted power switch with locking transparent cover prevents accidental shutoff
- 15 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332011459 |



| <b>INPUT</b>                                 |  |
|--|--|
| Nominal Input Voltage(s) Supported           | 120V AC  |
| Recommended Electrical Service               | 15A 120V   |
| Input Cord Gauge Type                        | 14 gauge; SJT  |
| Voltage Compatibility (VAC)                  | 120  |
| Input Plug Type                              | NEMA 5-15P   |
| Input Cord Length (ft.)                      | 15   |
| Input Cord Length (m)                        | 4.57   |
| Integrated Cord Clip                         | No   |
| <b>OUTPUT</b>                                |  |
| Frequency Compatibility                      | 50 / 60 Hz   |
| Output (Watts)                               | 1800   |
| Output Receptacles                           | (12) 5-15R   |
| Circuit Breaker (amps)                       | 15   |
| Transformer Accommodation                    | (6) Yes  |
| Right-Angle Outlets                          | No   |
| Outlet Spacing                               | 2.638 in.  |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |  |
| Switches                                     | Lighted 2 position switch controls power to all outlets  |
| Locking Switch Cover                         | Transparent on/off switch cover prevents accidental turn-off   |
| <b>PHYSICAL</b>                              |  |
| Antimicrobial Coating                        | No   |
| Color  | Silver   |
| Color (AC Line Cord)                         | Black  |
| Form Factors Supported                       | Supports horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications |
| Included Mounting Accessories                | Includes mounting clips  |
| Integrated Keyhole Mounting Slots            | No   |
| Material of Construction                     | Aluminum   |
| Outlets Measurement (Center to Center)       | 67mm   |
| Receptacle Color                             | Black  |
| Shipping Dimensions (hwd / cm)               | 100.33 x 8.38 x 5.08   |
| Shipping Dimensions (hwd / in.)              | 39.50 x 3.30 x 2.00  |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                           |
|-------------------------------------|---------------------------|
| Shipping Weight (kg)                | 2.01                      |
| Shipping Weight (lbs.)              | 4.44                      |
| Unit Dimensions (hwd / cm)          | 91.5 x 3.8 x 3.8          |
| Unit Dimensions (hwd / in.)         | 36 x 1.5 x 1.5            |
| Unit Weight (kg)                    | 1.72                      |
| Unit Weight (lbs.)                  | 3.8                       |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Canada                              | cUL                       |
| UL1363 (Power Tap)                  | UL1363                    |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>