

3-Outlet Power Strip - German Type F Schuko Outlets, 220-250V, 16A, 1.5 m Cord, Schuko Plug, White

MODEL NUMBER: PS3G15



3-outlet power strip distributes electricity to home and office electronics, including computers, power tools and appliances.

Features

25 cm Power Strip Delivers Electricity to 3 Devices at the Same Time Compatible with standard electrical equipment, this Protect It!® power strip features three Type F Schuko outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

Designed to Give You Flexibility in Placing the Power Strip Where It's Most Needed The power strip features a space-saving right-angle Schuko plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. The plug is attached to a 1.5-meter power cord, which gives you more choices in placing the power strip away from the connected AC outlet.

Premium Safety Features Designed for Protecting Your Valuable Equipment The PS3G15 features a lighted on/off switch that provides one-touch control over all connected devices. In the event of an overload, a 16-amp circuit breaker immediately shuts down the power strip to prevent equipment damage. The high-impact plastic housing is designed for the rigors of everyday use.

Highlights

- 3 Schuko outlets distribute power to appliances, tools, lighting and other electronics
- Right-angle Schuko plug permits connection in confined or hard-to-reach spaces
- 25 cm plastic housing designed to withstand the rigors of everyday use
- On/off switch gives you convenient one-touch control over all connected devices
- 16A circuit breaker shuts down all outlets for safety in case of overload

Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment

Package Includes

- PS3G15 3-Outlet Power Strip, German Type F Schuko Outlets, White

Specifications

OVERVIEW	
UPC Code	037332251619
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-240
Input Plug Type	German



Right-Angle Plug	Yes
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(3) Schuko Type F
Circuit Breaker (amps)	16
Overload Protection	combo switch/circuit breaker
Outlet Orientation	right-angled
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	White
Antimicrobial Coating	No
Color (AC Line Cord)	White
Housing Color	White
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic
Receptacle Color	White
Shipping Dimensions (hwd / cm)	24.89 x 7.37 x 5.08
Shipping Dimensions (hwd / in.)	9.80 x 2.90 x 2.00
Shipping Weight (kg)	0.34
Shipping Weight (lbs.)	0.75
SPECIAL FEATURES	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Approvals	CE, RoHS AND REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>